

## 4-Port UK-Style Gang Frame for 6C-Type Insert Module, White

MODEL NUMBER: **N042U-WF2-6C**



British-style gang frame accepts up to 4 compatible 6C-type modules for terminating premise data (Ethernet) applications.

### Features

#### U.K. Gang Frame Connects Your In-Wall Data Cable Line

This gang frame for 6C-type insert modules is ideal for terminating your data communications wiring application, including Gigabit Ethernet. The UK-style N042U-WF2-6C also protects electrical and network cables to help prevent accidental damage to your application.

#### High-Impact Construction Designed to Blend In Seamlessly with Your Room

This white gang frame measures 86 x 146 millimeters (outer frame) and accepts up to four 25 x 38.5 millimeter 6C-type insert modules. It blends elegantly into any home or office décor for a sleek, professional installation. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

### Highlights

- Ideal for completing a data (Ethernet) in-wall wiring installation
- Helps prevent accidental cable damage and hides unattractive wiring
- High-impact plastic construction designed to blend in with your home/office décor

### Package Includes

N042U-WF2-6C 4-Port UK-Style Gang Frame, White

## Specifications

OVERVIEW	
UPC Code	037332269553
Accessory Type	Wall Plate
Technology	Cat5/5e; Cat6; Cat6a
Country/Region	UK
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	(4) KEYSTONE JACK CUTOUT
PHYSICAL	



Powering Business Worldwide

TRIPP LITE  
SERIES

Color	White
Material of Construction	ABS
Total Number of Ports	4
Unit Dimensions (hwd / in.)	5.750 x 3.390 x 0.590
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 94; UL Listed; cUL Listed
Product Compliance	REACH; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N042U-WF2-6C](#)