

J-Hook Cable Support - 1-5/16", Wall Mount, Galvanized Steel, 25 Pack

MODEL NUMBER: NCM-JHW13-25



Galvanized wall-mount J-hooks help manage and organize category, fiber optic and other cables over long distances.

Features

J-Hooks: An Inexpensive Alternative to Cable Trays

These 1-5/16-inch wall-mount J-hooks are recommended for setting up network or digital signage installations that require cabling to be run along walls, ceilings and raised floors for long distances. NCM-JHW13-25 comes with 25 wall-mount J-hooks.

Designed to Accommodate a Wide Assortment of Cable Types

Less expensive and more flexible than cable trays or ladder rack runways, these J-hooks accommodate Cat5e/6/6a, fiber optic, audio/video, coaxial and other cable types. They comply with TIA-56B-C, TIA-569-C and ISO/IEC 14763-2 requirements for structured cabling systems, making them a perfect accessory for contractors, IT staff and cable installers.

Made from Galvanized Steel to Provide Proper Long-Term Support

These easy-to-install J-hooks are made from 18-gauge galvanized steel with a zinc-plated finish. To give you an idea of their strength, they offer stress-free support for up to 50 Cat5e cables, 40 Cat6 cables or 25 Cat6a cables. Maximum weight capacity is 60 pounds. Built-in anchor points allow you to use cable ties (sold separately) to secure cabling in place.

Highlights

- Recommended for network and digital signage cabling along walls and ceilings
- Made from galvanized steel designed to hold long lengths of cabling up to 60 lb.
- Offers stress-free support for wide range of cables, including fiber, A/V and Cat5e/6
- Built in anchor points allow use of cable ties to hold cables in place
- Package includes 25 wall-mount J-hooks that comply with TIA/EIA requirements

Applications

- Neatly bundle cable along a wall, ceiling or raised floor in your data center, network installation or digital signage setup

Package Includes

- (25) 1-5/16" J-Hooks, Wall Mount, Galvanized Steel

Specifications

| OVERVIEW | |
|-----------------|-------------------------|
| UPC Code | 037332236098 |
| Accessory Type | Cable Support |
| Accessory Class | Audio Video Accessories |
| PHYSICAL | |
| Color | Silver |

| | |
|-------------------------------------|--|
| Cable Jacket Color | Silver |
| Maximum Weight Capacity (lbs.) | 60 |
| Maximum Weight Capacity (kg) | 27 |
| Unit Dimensions (hwd / in.) | 4.130 x 1.400 x 1.300 |
| Unit Dimensions (hwd / cm) | 10.5 x 3.5 x 3.33 |
| Unit Weight (lbs.) | 0.1323 |
| Unit Weight (kg) | 0.06 |
| FEATURES & SPECIFICATIONS | |
| IP68 Rated | No |
| IP20 Rated | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | ISO/IEC 14763-2; RoHS; TIA-568-C; TIA-569-C; REACH |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[NCM-JHW13-25](#)