

# HDMI to DisplayPort Active Converter (M/F) with USB Power, 4K 60 Hz, 7 in. (18 cm)

MODEL NUMBER: P130-06N-DP-4K6



Connects an HDMI video/audio source device to a 4K DisplayPort monitor.

## Features

### Connects an HDMI Audio/Video Source to a 4K DisplayPort Monitor

The P130-06N-DP-4K6 lets you connect your existing 4K DisplayPort monitor or projector to an HDMI audio/video source, like a Blu-ray player, laptop or media server. Ideal for home theaters, trade shows, office presentations, lectures and digital signage, this active adapter video converter saves you the extra cost of adding a new HDMI display to your application.

### Transmits 4K Video and Digital Audio with HDR and 4:4:4 Color

The P130-06N-DP-4K6 supports Ultra HD 4K resolutions up to 3840 x 2160 at 60 Hz with 7.1-channel surround sound and 36-bit True Color. It supports High Dynamic Range (HDR), providing a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.2 encryption allows you to stream 4K content with no loss in resolution. This adapter also supports uncompressed 4:4:4 chroma subsampling for top-level PC gaming or for using your HDTV as a PC monitor.

### Also Connects a DVI or Mini-DVI Source

With an optional HDMI-to-DVI or -mini-DVI adapter (such as the P566 Series, sold separately), you can also use this active converter to connect your 4K DisplayPort monitor to a DVI or mini-DVI source.

### Plug-and-Play Operation for Quick Setup and Immediate Use

The HDMI-to-DisplayPort converter works right out of the box with no software required. If extra power is needed, connect its built-in USB plug to your laptop's USB-A port. This cable is small enough to fit into your briefcase, backpack or laptop bag so you can take it with you wherever you go.

## Specifications

OVERVIEW	
UPC Code	037332288646
Product Type	Video Adapter
Technology	DisplayPort; HDMI

## Highlights

- Recommended for home theaters, digital signage, trade shows and classrooms
- Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) with High Dynamic Range (HDR)
- Delivers robust 7.1-channel surround sound to your display's speakers
- Plug-and-play operation: no software required means easy, immediate installation

## System Requirements

- Source device with HDMI output (Blu-ray player, media server, laptop)
- Display device with DisplayPort input (HDTV, projector, monitor)
- Connected device must support 4K video resolution to achieve 4K display

## Package Includes

- P130-06N-DP-4K6 4K HDMI to DisplayPort Active Converter, M/F, 7 in. (18 cm)
- Installation instructions

VIDEO	
Video Input	HDMI (FEMALE)
Video Output	DISPLAYPORT (MALE)
Max Supported Video Resolution	4096 x 2160 (4K X 2K) @ 60Hz
Max Supported Color Depth	24-bit True Color
HDR Support	Yes
3D Video Supported	No
Chroma Sub Sampling	4:2:2; 4:4:4
DisplayPort Alt Mode	No
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	DISPLAYPORT (FEMALE); USB A (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Material of Construction	PVC + ABS
Cable Jacket Color	Black
Connector Color	Gold
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.8MM
Wire Gauge (AWG)	32
Cable Length (ft.)	0.6
Cable Length (m)	0.18
Cable Length (in.)	7.1
Shipping Dimensions (hwd / in.)	0.85 x 3.90 x 4.70
Shipping Weight (kg)	0.08
Unit Dimensions (hwd / in.)	0.500 x 1.000 x 10.000
Unit Packaging Type	Box
Unit Weight (lbs.)	0.09
Unit Weight (kg)	0.04



Powering Business Worldwide

TRIPP LITE  
SERIES

<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	14° to 176°F (-10° to 80°C)
Operating Humidity Range	10% TO 85% RH, NON-CONDENSING
Storage Humidity Range	5% TO 90% RH, NON-CONDENSING
<b>COMMUNICATIONS</b>	
EDID Compatible	No
Consumer Electronics Control (CEC) Supported	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
EMI/RFI Line Noise Protection	No
Integrated/Removable Cable	No
MST Support	No
Antibacterial	No
Fully Molded Connector Ends	No
Ohms	No
Integral Strain Relief	No
Impedance-Matched Twisted-Pair Construction	No
Scaler Function	No
IP67 Rated	No
Armored Cable	No
Displayport Specification	1.2
HDCP Specification	1.4
Driver Required	No
DIN Mountable	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	CE (Europe); FCC Part 15 Class B (USA); RoHS; UKCA; WEEE
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[P130-06N-DP-4K6](#)