

DisplayPort to DVI-I Adapter Cable (M/F), 6 in. (15.2 cm)

MODEL NUMBER: **P134-000**



Features

- Connect a DVI monitor to a computer with a DisplayPort output
- DisplayPort to DVI Adapter Converter (DisplayPort-Male to DVI-I-Female), 6 in.
- Supports DVI-D single-link computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- Fully molded ends
- The P134-000 is a passive adapter, and requires to be connected to any Displayport 1.1/1.2/1.4/2.1 version graphics card with Dual Mode DP++ (DisplayPort ++) port, which allows HDMI and DVI signals to be passed through; check the documentation for your DisplayPort source for compatibility.

Highlights

- Connect a DVI monitor to a computer with a DisplayPort output
- Adapter cable connects DVI monitor to any DisplayPort 1.1/1.2/1.4/2.1 version dual-mode port
- DisplayPort to DVI Adapter Converter (DisplayPort-Male to DVI-I-Female), 6 in.
- Plug-and-play convenience; no drivers or software needed
- Supports DVI-D single-link computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode port
- HDCP 1.x or 2.x version & DDC pass-through ensure compatibility between source & display

System Requirements

- A computer with a DisplayPort output
- A monitor with a DVI port
- The P134-000 is a passive adapter, and requires that the connected computer has a DP++ (DisplayPort ++) port, which allows HDMI and DVI signals to be passed through; check the documentation for your DisplayPort source for compatibility
- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P134-06N-DVI-V2

Package Includes

- DisplayPort to DVI Adapter Converter (DisplayPort-Male to DVI-I-Female)

Specifications

OVERVIEW

UPC Code

037332148292



Powering Business Worldwide

TRIPP LITE
SERIES

Product Type	Passive Cable
Device Compatibility	Computer; DVR; Laptop; Monitor/HDTV; Projector; Server
Technology	DVI; DisplayPort
Cable Type	Passive
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.16
Shipping Weight (kg)	0.07
Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
Unit Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Unit Weight (lbs.)	0.16
Unit Weight (kg)	0.07
STANDARDS & COMPLIANCE	
Product Certifications	2MOPP
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P134-000](#)