

DisplayPort to DVI Cable Adapter, Converter for DP-M to DVI-I-F, 6-in. (15.24 cm), 50 Pack, TAA

MODEL NUMBER: P134-000-50BK



Passive adapters connect your computer or tablet's DisplayPort™ to the DVI input on a monitor, projector or television. Source devices must have DisplayPort++ (DP++) for HDMI/DVI pass-through.

Features

Send High-Definition DisplayPort Video Signals to a DVI Display

- Connects DisplayPort computer or tablet to DVI-enabled monitor, projector or TV
- Recommended for digital signage or presentations in a classroom or conference room
- Male DisplayPort and female DVI-I dual-link connectors
- Connect to any Displayport 1.1/1.2/1.4/2.1 version graphics card with Dual Mode DP++ (DisplayPort ++) port, which allows HDMI and DVI signals to be passed through; check the documentation for your DisplayPort source for compatibility.
- Bulk pack includes 50 P134-000 DisplayPort to DVI converters

Vibrant Video Quality

- Supports DVI-D single-link video resolutions up to 1920 x 1200
- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Passive adapter requires source device to have DP++ compatibility for HDMI/DVI signal pass-through

Superior Materials for Superior Performance

- Foil and braid shielding helps protect against EMI/RFI line noise that can distort or destroy data
- Molded connectors and gold-plated contacts for maximum conductivity and minimum data loss
- Integral strain relief protects cable and connectors from stress and cracking

Convenient to Use Anywhere

- Plug-and-play—no software, drivers or power supply necessary
- Fits easily into briefcase, backpack or laptop bag

Specifications

Highlights

- Connect a DVI monitor to a computer with a DisplayPort output
- Adapter cable connects DVI monitor to any DisplayPort 1.1/1.2/1.4/2.1 version dual-mode port
- DisplayPort to DVI Adapter Converter (DisplayPort-Male to DVI-I-Female), 6 in.
- Plug-and-play convenience; no drivers or software needed
- Supports DVI-D single-link computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode port
- HDCP 1.x or 2.x version and DDC pass-through ensure compatibility between source and display

System Requirements

- Source device with DisplayPort output
- Display device with DVI input
- Source must have DP++ port for HDMI/DVI pass-through
- Not for use with MST hubs

Package Includes

- (50) P134-000 DisplayPort to DVI Cable Adapters (M/F), 6 in.



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|--|
| UPC Code | 037332205506 |
| Product Type | Video Adapter |
| Device Compatibility | Computer; DVR; Laptop; Monitor/HDTV; Projector; Server |
| Technology | DVI; DisplayPort |
| CONNECTIONS | |
| Side A - Connector 1 | DISPLAYPORT (MALE) |
| Side B - Connector 1 | DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK) |
| PHYSICAL | |
| Color | Black |
| Cable Jacket Color | Black |
| Cable Length (ft.) | 0.5 |
| Cable Length (m) | 0.15 |
| Cable Length (in.) | 6 |
| Cable Length (cm) | 15.24 |
| Shipping Dimensions (hwd / in.) | 6.33 x 11.88 x 6.75 |
| Shipping Dimensions (hwd / cm) | 16.08 x 30.18 x 17.14 |
| Shipping Weight (lbs.) | 6.00 |
| Shipping Weight (kg) | 2.72 |
| Unit Dimensions (hwd / in.) | 0.000 x 0.000 x 0.000 |
| Unit Dimensions (hwd / cm) | 16.08 x 30.18 x 17.14 |
| Unit Weight (lbs.) | 6.0 |
| Unit Weight (kg) | 2.72 |
| STANDARDS & COMPLIANCE | |
| Product Certifications | 2MOPP |
| Product Compliance | Trade Agreements Act (TAA) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P134-000-50BK](#)