

DisplayPort to DVI Dual-Link Active Adapter Video Converter (M/F), 6-in. (15.24 cm)

MODEL NUMBER: P134-06N-DVI-DL



Converts any DisplayPort video signal for display on a DVI-I single-link or dual-link monitor, projector or television.

Features

Send High-Definition DisplayPort Video Signals to a DVI Display Connects DisplayPort computer to DVI-I dual-link monitor, projector or TV Active converter works with all DisplayPort signals Ideal for displaying video on large monitor or digital sign Female DVI dual-link and male DisplayPort connectors

Vibrant, Superior Video Quality Supports DVI dual-link video resolutions up to 2560 x 1600 Supports DVI single-link video resolutions up to 1920 x 1080 (1080p) Supports 24-bit Deep Color (8 bits per channel) Converts Multi-Mode (DP++) and Single-Mode DisplayPort output Works with graphics cards that don't output DP++ signals, such as AMD Eyefinity

Superior Materials for Superior Performance Gold-plated connectors and contacts for excellent conductivity Integral strain relief for long life Plug-and-play—no software, drivers or power supply necessary Fits easily into briefcase, backpack or laptop bag

Specifications

OVERVIEW	
UPC Code	037332198716
Product Type	Video Adapter
Technology	DVI; DisplayPort
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side A - Connector 2	USB A (MALE)
Side B - Connector 1	DVI-I DUAL LINK (FEMALE) (WIRED TO DVI-D DUAL LINK)

Highlights

- Active converter works with all DisplayPort signals
- Supports DVI dual-link video resolutions up to 2560 x 1600
- Supports DVI single-link video resolutions up to 1920 x 1080
- Converts Multi-Mode (DP++) and Single-Mode DisplayPort output
- Plug and play—no software, drivers or power supply needed

System Requirements

- Computer with DisplayPort and USB port
- Display with DVI output
- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P134-06N-DVI-V2

Package Includes

- P134-06N-DVI-DL DisplayPort to DVI Dual-Link Active Converter (M/F), 6 in.

PHYSICAL	
Color	Silver
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	1.30 x 3.50 x 6.20
Shipping Dimensions (hwd / cm)	3.30 x 8.89 x 15.75
Shipping Weight (lbs.)	0.35
Shipping Weight (kg)	0.16
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P134-06N-DVI-DL](#)