

Mini DVI to DVI Cable Adapter, Video Converter for Macbooks and iMacs, 1920x1200 (Mini DVI to DVI-D M/F)

MODEL NUMBER: P138-000-DVI



Highlights

- Connect a DVI Monitor to Apple Intel iMac, MacBook, and 12in PowerBook G4 mini-DVI Port
- 8 in. overall length

System Requirements

- Apple Intel iMac, MacBook, and 12in PowerBook G4

Package Includes

- 8-in. mini-DVI to DVI-D Adapter

Description

This mini-DVI to DVI-D Digital Female Video Adapter Cable allows you to connect a DVI-D Display to the mini-DVI port found on some Apple computer models. Supports Single-Link digital transmission with resolutions up to 1920 x 1200 at 60 Hz.

Features

- Connect a DVI Monitor to Apple Intel iMac, MacBook, and 12-in. PowerBook G4 mini-DVI Port
- 8 in. overall length
- 1920x1200 @ 60Hz resolution

Specifications

OVERVIEW	
UPC Code	037332152138
Product Type	Video Adapter
Device Compatibility	Computer; Laptop; Tablet
Technology	DVI
CONNECTIONS	
Side A - Connector 1	MINI-DVI (MALE)
Side B - Connector 1	DVI-D DUAL LINK (FEMALE)
PHYSICAL	
Color	White



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Jacket Color	White
Cable Length (ft.)	0.7
Cable Length (m)	0.21
Cable Length (in.)	8
Cable Length (cm)	20.32
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.31
Shipping Weight (kg)	0.14
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Unit Weight (lbs.)	0.14
Unit Weight (kg)	0.06
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P138-000-DVI](#)