


## Slim High-Speed HDMI Cable with Ethernet and Digital Video with Audio, UHD 4K 60Hz (M/M), 3 ft. (0.91 m)

MODEL NUMBER: **P569-003-SLIM**



Transmits digital audio/video and Ethernet signals from an HDMI source to a 4K-enabled television, projector or monitor. Recommended for home theater systems and digital signage. Slim design increases airflow in tight spaces.

### Features

#### Connects HDMI Source to 4K TV, Projector or Monitor

- Ideal for home theater systems, digital signage and other applications that display UHD video and multi-channel audio

#### High Performance and Wide Compatibility

- Supports UHD video resolutions up to 4K 60Hz, and 3D
- Audio return channel simplifies setup between display and receiver
- Supports iPad2 video mirroring when used with Apple digital A/V adapter
- Backward compatible with previous HDMI generations
- Works in all HDMI cabling scenarios

#### Special Slim Design

- Improved airflow in tight spaces
- Better flexibility for installing around corners and through cable management panels

#### Superior Construction Ensures a Flawless Signal

- Fully molded 36 AWG construction with integral strain relief for durability and long life
- Premium foil and braid shielding for EMI/RFI noise protection
- Corrosion-resistant gold-plated connectors and contacts for optimal signal transfer
- Flexible PVC jacket easy to install in tight spaces

### Highlights

- Supports UHD video resolutions up to 4K 60Hz
- Easy to install around corners and through management panels
- Premium foil and braid shielding protects against EMI/RFI noise
- Gold-plated connectors and contacts for optimal signal transfer

### Package Includes

- P569-003-SLIM Slim High-Speed HDMI Cable with Ethernet and Digital Video with Audio (M/M), 3 ft.

## Specifications

### OVERVIEW



Powering Business Worldwide

TRIPP LITE  
SERIES

UPC Code	037332199355
Product Type	Passive Cable
Technology	HDMI
Cable Type	Passive
<b>VIDEO</b>	
Max Supported Video Resolution	3840 x 2160 (4K) @ 30Hz
Max Supported Color Depth	24-bit True Color
HDR Support	No
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
EDID Support	Yes
Signal Transmission	Bidirectional
<b>AUDIO</b>	
Audio Specification	Stereo Audio
<b>CONNECTIONS</b>	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
Connector Plating	Gold
Contact Plating	Gold
Connector Style	Straight
Latching or Gripping Connector	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	0
<b>PHYSICAL</b>	
Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.6 mm
Wire Gauge (AWG)	34
Cable Length (ft.)	3
Cable Length (m)	0.91



Powering Business Worldwide

TRIPP LITE  
SERIES

Cable Length (in.)	36
Ferrite Core	No
Minimum Bend Radius	36mm
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.07
Shipping Weight (kg)	0.03
Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	-40° to 176°F (-40° to 80°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Consumer Electronics Control (CEC) Supported	Yes
<b>FEATURES &amp; SPECIFICATIONS</b>	
EMI/RFI Line Noise Protection	No
MST Support	No
Antibacterial	No
IP68 Rated	No
IP20 Rated	No
Armored Cable	No
Ethernet Support	Yes
HDCP Specification	1.4
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P569-003-SLIM](#)