

Daisy Chain Cable for NetController KVM Switches B040-Series and B042-Series, 10 ft. (3.05 m)

MODEL NUMBER: P781-010



Highlights

- Molded HD15 Male/Female, 10-ft. (3.05 m)
- Double Shielded
- For Daisy Chaining B040 and B042 KVM switches

System Requirements

Use only with B040 and B042 series KVM switches, to daisy chain additional KVM switches.

Package Includes

10-ft. (3.05 m) HD15 Male/Female B040 / B042 KVM Daisy Chain Cable

Description

Molded HD15 Male/Female Daisy-Chain cable, specifically wired for B040- and B042-Series KVM switches. Double shielded and fully molded construction for optimum video transfer and long life.

Features

- Daisy Chain cable for B040 and B042 series KVM switches
- Fully molded construction, with double shielding
- HD15 Male/Female 10-ft. (3.05 m)

Specifications

OVERVIEW	
UPC Code	037332146502
Accessory Type	Daisy-Chain Cable
Accessory Class	KVM Switch Accessories
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	0.50 x 6.00 x 7.00
Shipping Dimensions (hwd / cm)	1.27 x 15.24 x 17.78

Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P781-010](#)