

2-Outlet Power Strip - British BS1363A Outlets, 220-250V AC, 13A, Direct Plug, BS1363A Plug, White

MODEL NUMBER: **PS1B**



2-outlet power strip distributes electricity to home and office electronics, including computers, power tools and appliances.

Features

Compact Power Strip Delivers Electricity to 2 Devices at the Same Time Compatible with standard electrical equipment, this Protect It!® power strip plugs directly into a wall outlet (no cord required). It features two BS1363A outlets and a durable white plastic housing. It is ideal for powering almost anything with a compatible plug, including computers and mobile devices to appliances and power tools.

Compact High-Impact Housing Makes Connecting in Tight Spaces Easier This direct-plug power strip is easy to install in confined spaces, such as behind furniture. One outlet is located on top of the unit, so a connected power cord runs parallel to the wall, allowing you to push furniture against the wall to maximize space.

Premium Safety Features Designed for Protecting Your Valuable Equipment An integrated 13A circuit breaker protects all outlets and automatically cuts power if the protection circuit is incapacitated, preventing equipment damage and indicating replacement is required.

Highlights

- BS1363A outlets distribute power to appliances, tools, lighting and other electronics
- Plugs directly into the wall (no cord required) for easy installation in tight spaces
- 13A circuit breaker shuts down both UK outlets for safety in case of overload

Applications

- Distribute power to computer equipment and other devices in an office, workbench, retail or telecom environment

Package Includes

PS1B 2-Outlet Direct-Plug Power Strip, BS1363A Outlets, White

Specifications

OVERVIEW	
UPC Code	037332251572
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250
Input Plug Type	British



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(2) British BS 1363A
Circuit Breaker (amps)	13
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Color	White
Material of Construction	Plastic
Power Cord Color	White
Housing Color	White
Mounting Holes or Slots	Yes
Receptacle Color	White
Shipping Dimensions (hwd / in.)	2.00 x 4.70 x 2.90
Shipping Dimensions (hwd / cm)	5.08 x 11.94 x 7.37
Shipping Weight (lbs.)	0.25
Shipping Weight (kg)	0.11
Unit Dimensions (hwd / in.)	2.000 x 2.200 x 2.800
Unit Dimensions (hwd / cm)	11.6 x 2.9 x 2.9
Unit Weight (lbs.)	0.81
Unit Weight (kg)	0.37

FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PS1B](#)