

## Important Note

UL1363a, Paragraph 14.1(d) States "The SPRPT shall be permanently attached to the medical equipment by a means such that it is only removable with the use of a tool." To achieve compliance, one must use the PSCLAMP.

## Safe-IT UL 1363A Medical-Grade Power Strip for Patient-Care Vicinity, 4x 15A Hospital-Grade Outlets, 2 ft. Cord

MODEL NUMBER: PS-402-HG-OEM



Supplies power to movable plug-connected components mounted to IV poles, mobile carts, crash carts and mobile medical workstations in operating rooms and patient-care vicinities.

## Description

The PS-402-HG-OEM Medical-Grade Power Strip supplies power to movable plug-connected components mounted to a rack, table or pedestal in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and four NEMA 5-15R-HG hospital-grade outlets.

The power strip is protected by an antimicrobial powder coating. Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Two built-in resettable 15A circuit breakers control power to all outlets and protect the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. The two-foot (0.6-meter) power cord eliminates excess cordage that needs to be wrapped.

Mounting tabs and flanges let you install the PS-402-HG-OEM on a wide variety of surfaces, such as IV poles, mobile carts, crash carts and mobile medical workstations. The all-metal housing ensures safety and is guaranteed to last a long time in demanding environments.

## Features

**Power Distribution Anywhere in Any Medical Facility** Ideal for use in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas For use on IV poles, mobile carts, crash carts and mobile workstations, when properly mounted 120V, 50/60 Hz power strip complies with UL 1363A specifications

**Exclusive Antimicrobial Protection** Antimicrobial coating helps resist the growth of bacteria, viruses, fungi, mold and mildew Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

**Versatile Medical-Grade Solution** 4 NEMA 5-15R-HG hospital-grade outlets provide consistent power 2-

## Highlights

- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Approved for use in patient-care vicinities when properly mounted
- Complies with UL 1363A & NFPA 99 specifications
- Features 4 NEMA 5-15R-HG hospital-grade outlets
- Includes 2 ft. (0.6 m) cord with NEMA 5-15P-HG hospital-grade plug

## Package Includes

- PS-402-HG-OEM UL 1363A Medical-Grade Power Strip with 4 15A Hospital-Grade Outlets and 2-ft. (0.61 m) Cord
- Owner's Manual with maintenance requirements



Powering Business Worldwide



ft. (0.61 m) power cord eliminates excess cordage that needs to be wrapped up  
Rugged, all-metal housing for long life in demanding environments

**Premium Safety Features** Dual, resettable built-in 15A circuit breakers protect against dangerous overloads  
Switchless design prevents accidental shut-off

**Ready to Use Right Out of the Box** Built-in mounting tabs and flanges make the PS-402-HG-OEM easy to install on a variety of surfaces

## Specifications

OVERVIEW	
UPC Code	037332147998
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Plug Features	Hospital Grade Plug
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	2
Right-Angle Plug	No
Input Cord Length (m)	0.61
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Color	White



Powering Business Worldwide

**TRIPP-LITE**  
by **EAT•N**

Material of Construction	Metal
Power Cord Color	White
Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations
Housing Color	White
Included Mounting Accessories	Mounting tabs and flanges
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm
Outlets Measurement (Center to Center)	Inner outlets = 1.27 in.
Receptacle Color	White
Shipping Dimensions (hwd / in.)	2.36 x 6.10 x 9.76
Shipping Dimensions (hwd / cm)	5.99 x 15.49 x 24.79
Shipping Weight (lbs.)	1.64
Shipping Weight (kg)	0.74
Unit Dimensions (hwd / in.)	1.730 x 2.500 x 8.540
Unit Dimensions (hwd / cm)	4.39 x 6.35 x 21.7
Unit Weight (lbs.)	1.45
Unit Weight (kg)	0.66
Mounting Details	Includes flanges
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	Yes
Built-In Circuit Breaker	Yes
Antibacterial	No
Built-in Cable Management	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 1363A
Product Compliance	NFPA 99: 10.2.3.6; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PS-402-HG-OEM](#)