

## Industrial Power Strip, 6-Outlet, 4 ft. (1.2 m) Cord

MODEL NUMBER: PS6



### Highlights

- 6 outlets
- 4-ft. (1.22 m) cord
- 9.5-inch length
- Master on/off switch

### Package Includes

- PS6 Power Strip
- Warranty information
- Instruction manual

### Description

The PS6 Power Strip offers a convenient method of power distribution in workbench, wall-mount or floor-mount applications. Includes six NEMA 5-15R outlets, 4-ft. (1.22 m) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the PS6 ideal for distributing alternate waveform UPS or generator power. Features power switch, circuit breaker and attractive gray color scheme.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip

### Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles
- Power switch
- 15A circuit breaker
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15A power handling capacity
- 4-ft. (1.22 m) AC line cord

## Specifications

OVERVIEW	
UPC Code	037332116123
INPUT	
Nominal Input Voltage(s) Supported	120V AC



Powering Business Worldwide

**TRIPP-LITE**  
by **EAT•N**

Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	4
Right-Angle Plug	No
Input Cord Length (m)	1.22
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Master on/off switch with separate circuit breaker
<b>PHYSICAL</b>	
Color	Light Gray
Material of Construction	Plastic
Power Cord Color	Light Gray
Housing Color	Gray
Mounting Holes or Slots	Yes
Receptacle Color	Light gray
Shipping Dimensions (hwd / in.)	10.60 x 2.00 x 3.60
Shipping Dimensions (hwd / cm)	26.92 x 5.08 x 9.14
Shipping Weight (lbs.)	0.83
Shipping Weight (kg)	0.38
Unit Dimensions (hwd / in.)	1.200 x 1.700 x 9.450
Unit Dimensions (hwd / cm)	3.05 x 4.32 x 24.01
Unit Weight (lbs.)	.77
Unit Weight (kg)	0.35
<b>FEATURES &amp; SPECIFICATIONS</b>	

Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PS6](#)