

Important Note

UL1363a, Paragraph 14.1(d) states, "The SPRPT shall be permanently attached to the medical equipment by a means such that it is only removable with the use of a tool." To achieve compliance, one must use the PSCLAMP.

Safe-IT UL 1363A Medical-Grade Power Strip for Patient-Care Vicinity, 6x Hospital-Grade Outlets, 15 ft. Right-Angle Cord

MODEL NUMBER: PS-615-HG-OEMRA



Delivers power to devices attached to IV poles, crash carts and mobile workstations in operating rooms and other patient care vicinities.

Features

6-Outlet Medical-Grade Power Strip with Long 15 ft. Cord Approved for Patient Care Vicinities PS-615-HG-OEMRA supplies power to movable plug-connected components mounted to IV poles, mobile carts, crash carts and mobile medical workstations inside and outside patient care vicinities when properly mounted. This includes operating rooms, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V power strip features six NEMA 5-15R-HG hospital-grade outlets.

Exclusive Antimicrobial Protection Fights Healthcare-Acquired Infections (HAIs) The power strip is protected by a patented antimicrobial powder coating with EPA-registered and FDA-compliant silver ionic technology. The antimicrobial surface protection is 99.9 percent effective in inhibiting the growth of bacteria and reducing the risk of HAIs in hospitals and other medical environments. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Premium Safety Features Help Ensure Proper Power Connections With no central power switch, this power strip presents no danger of accidental shutoff and cutting off power to essential devices. Two resettable 15-amp circuit breakers will shut down all AC input if the power strip determines the connected equipment load is drawing too much power. Six locking plastic safety covers are included to block access to unused outlets.

Ready for Installation in Demanding Medical Environments The power strip with 15-foot (4.6-meter) cord also includes a space-saving right-angle NEMA 5-15P-HG plug that helps you connect to a wall outlet located behind furniture that is placed flush against the wall. Built-in mounting flanges and integrated keyhole slots let you install the durable all-metal housing on any mobile cart or IV pole for distributing power to movable rack-, table- and pedestal-mounted equipment.

Highlights

- UL 1363A power strip for use inside and outside patient care vicinities
- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Complies with NFPA 99
- Right-angle 5-15P-HG plug permits connection in confined or hard-to-reach spaces
- 15 ft. (4.6 m) power cord allows flexibility in placing power strip in relationship to AC outlet
- Switchless design helps prevent accidental shutdown of essential equipment

Applications

Supply safe medical-grade power to lab, imaging and other electric components mounted to an IV pole or crash cart in a patient care area

Package Includes

- PS-615-HG-OEMRA Medical-Grade Power Strip, 6 Outlets, 15-ft. (4.57 m) Cord
- (6) Outlet safety covers
- Owner's manual



Powering Business Worldwide



Specifications

OVERVIEW	
UPC Code	037332239457
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Plug Features	Right-Angle Hospital Grade Plug
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Right-Angle Plug	Yes
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Color	White
Material of Construction	Metal
Power Cord Color	White
Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations
Housing Color	White



Powering Business Worldwide



Included Mounting Accessories	Mounting tabs and flanges
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between end tabs = 330.20mm
Outlets Measurement (Center to Center)	1.52 in.
Receptacle Color	White
Shipping Dimensions (hwd / in.)	2.20 x 5.70 x 14.40
Shipping Dimensions (hwd / cm)	5.59 x 14.48 x 36.58
Shipping Weight (lbs.)	3.50
Shipping Weight (kg)	1.59
Unit Dimensions (hwd / in.)	1.500 x 13.750 x 2.500
Unit Dimensions (hwd / cm)	34.93 x 6.35 x 3.81
Unit Weight (lbs.)	2.25
Unit Weight (kg)	1.02
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	Yes
Built-In Circuit Breaker	Yes
Antibacterial	No
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 1363A
Product Compliance	NFPA 99: 10.2.3.6; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PS-615-HG-OEMRA](#)