

UPS Replacement Battery Cartridge for Select AVR550U/AVRX550U UPS Systems, 12V

MODEL NUMBER: RBC36H



UPS backup battery replacement breathes new life into a Tripp Lite UPS system suffering from expired or weak internal batteries.

Features

UPS Replacement Battery Cartridge for Select UPS Systems This UPS backup battery replacement is designed for these specific battery-door enabled versions of AVR550U, AVRX550U, ECO550UPS, ECO650UM, INTERNET550SER, INTERNET550U and INTERNET600U that originally shipped with a 12V 3.6Ah battery inside. It is carefully screened and certified to meet or exceed original runtime specifications. The leakproof, no-maintenance RBC36H comes ready for quick and easy installation in your UPS system. It functions within a wide range of operating temperatures. Reusable packaging allows you to easily send expired batteries to a recycling center.

Highlights

- Replacement battery backup for select AVR550U and AVRX550U UPS systems
- Compatible with AVR550U or AVRX550U UPS that shipped with 12V 3.6Ah battery
- Carefully screened and certified to restore UPS runtime to original specs
- Leakproof internal battery requires no regular maintenance
- Ships fully assembled and ready for immediate installation to prevent downtime

Applications

- Replace the aging or expired internal battery in your Tripp Lite AVR550U or AVRX550U UPS system

System Requirements

- Battery door enabled versions of AVR550U, AVRX550U, ECO550UPS, ECO650UM, INTERNET550SER, INTERNET550U and INTERNET600U UPS system that originally shipped with a 12V 3.6Ah battery inside

Package Includes

- RBC36H UPS Battery Replacement Cartridge
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332251480
BATTERY	
Included Battery Set	Contains (1) 12V 3.6AH sealed lead acid battery
Typical Battery Lifespan	3 - 5 years, depending on host UPS operating conditions
PHYSICAL	
Shipping Dimensions (hwd / in.)	3.66 x 2.83 x 4.96
Shipping Weight (kg)	1.02



Powering Business Worldwide



Unit Dimensions (hwd / in.)	2.760 x 1.890 x 4.020
Unit Dimensions (hwd / cm)	7.01 x 4.8 x 10.21
Unit Weight (lbs.)	2.05
Unit Weight (kg)	0.93
ENVIRONMENTAL	
Relative Humidity	0 - 95% non-condensing
Operating Elevation	0-10000 ft. (0-3000 m)
Storage Elevation (ft.)	0 - 50,000
Storage Elevation (m)	0 - 15,200 m
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[RBC36H](#)