

Internal SAS Cable, 4-Lane mini-SAS (SFF-8087) to 4xSata 7pin, 18-in. (0.5M)

MODEL NUMBER: **S508-18N**



Highlights

- Positive and passive latching ensures that the plug remains mated to receptacle
- All internal Mini-SAS assemblies are capable of supporting SAS/SATA generation I, II, and III bandwidths (up to 6Gbps)
- Reduced mechanical size offers up to 4 times the port density of the current x4 solution

Package Includes

- 18 in. Internal SAS Cable, SFF-8087 to 4 x 7pin SATA

Description

Internal Mini-SAS SFF-8087 to 4 x SATA 7pin cable, 18 inches long. Controller to four drives.

Features

- Positive and passive latching ensures that the plug remains mated to receptacle
- All internal mini SAS assemblies are capable of supporting SAS/SATA generation I, II, and III bandwidths (up to 6Gbps)
- Reduced mechanical size offers up to 4 times the port density of the current x4 solution
- For Controller to hard drive applications

Specifications

OVERVIEW	
UPC Code	037332143358
Technology	SAS; SATA/eSATA; Ribbon/Internal
CONNECTIONS	
Side A - Connector 1	SFF-8087
Side B - Connector 1	7 PIN SATA (MALE)
PHYSICAL	
Color	Red
Cable Jacket Color	Red
Cable Length (ft.)	1.5

Cable Length (m)	0.46
Cable Length (in.)	18
Cable Length (cm)	45.72
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.09
Shipping Weight (kg)	0.04
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[S508-18N](#)