

# External SAS Cable, 4 Lane - mini-SAS (SFF-8088) to mini-SAS (SFF-8088), 1M (3.28 ft.)

MODEL NUMBER: S524-01M



## Highlights

- High-performance 1-meter SAS external cable
- Mini-SAS SFF-8088 ( iSAS ) to Mini-SAS SFF-8088 ( iSAS )

## System Requirements

- SAS Controllers, SAS Chassis, SAS/SATA Hard Drives

## Package Includes

- 1-Meter SAS External, SFF-8088 to SFF-8088 Cable

## Features

- 1-meter External SAS Cable, SFF-8088 to SFF-8088
- Made with High-Performance Infiniband Cable
- Support data rates from 3.0 up to 6.0 gigabytes per second
- SFF-8088 connectors in diecast zinc housing for durability
- RoHS compliant

## Specifications

OVERVIEW	
UPC Code	037332139078
Technology	SAS
CONNECTIONS	
Side A - Connector 1	SFF-8088
Side B - Connector 1	SFF-8088
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	3.3
Cable Length (m)	1.01
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 10.00

Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 25.40
Shipping Weight (lbs.)	0.32
Shipping Weight (kg)	0.15
Unit Dimensions (hwd / in.)	0.500 x 7.000 x 10.000
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[S524-01M](#)