

25U SmartRack 2-Post Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: SR2POST25



Highlights

- 25U 2-post open frame rack
- Black aluminum with 12-24 threaded and numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

Package Includes

- SR2POST25
- 28 pieces each of 12-24 screws and washers for equipment mounting
- Installation hardware
- Cable management hooks
- Warranty Information
- Owner's Manual

Description

SR2POST25 2-Post SmartRack® Open Frame Rack is an economical way to accommodate 25U of rack space for 19-inch rack-mount applications in limited spaces that do not require a lockable enclosure. Its heavy-duty, aluminum construction can safely support 800 pounds (362.9 kilograms) of rack-mount equipment, and its open design provides easy access to equipment and cabling. The black, textured powder coat finish makes it resistant to scratching while giving it a "classic" attractive appearance. The SR2POST25 is easy to install due to a self-squaring design combined with 12-24 threaded and numbered mounting positions and bolt-down provisions. It uses toolless button-hole mounting for vertical PDUs and cable managers. In high-density environments, multiple units can be bolted together side by side for easy expansion or customization. The SR2POST25 2-Post SmartRack Open Frame Rack has been approved by EIA-310-D, IEC 60297-3-100 and RoHS.

Features

- Supports 800 lbs (362.9 kgs) of rackmount equipment
- Textured powder coat finish
- Heavy Duty Aluminum construction
- 12-24 threaded and numbered mounting positions
- Toolless button holes to accept PDUs or cable managers
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly

Specifications

OVERVIEW	
UPC Code	037332143143
Device Compatibility	Patch Panel; Network Switch; UPS; Server



Powering Business Worldwide



Rack Type	Open-Frame
PHYSICAL	
Color	Black
Rack Height	25U
Rack Depth	Extra Deep
EIA Mounting Rails	12-24 threaded and numbered mounting positions
Maximum Device Depth (cm)	121.92
Maximum Device Depth (in.)	48
Maximum Device Depth (mm)	1,219
Shipping Dimensions (hwd / in.)	4.50 x 6.00 x 52.60
Shipping Dimensions (hwd / cm)	11.43 x 15.24 x 133.60
Shipping Weight (lbs.)	26.00
Shipping Weight (kg)	11.79
Unit Dimensions (hwd / in.)	49.010 x 20.300 x 13.500
Unit Dimensions (hwd / cm)	124.46 x 51.56 x 12.06
Unit Weight (lbs.)	23
Unit Weight (kg)	10.43
Weight Capacity - Stationary (kg)	363
Weight Capacity - Stationary (lbs.)	800
Number of Vertical Mounting Rails	2
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SR2POST25](#)