

45U SmartRack 4-Post Open Frame Rack - Threaded 12-24 Mounting Holes

MODEL NUMBER: **SR4POST1224**



Highlights

- 45U 4-post open frame rack
- Black steel with threaded (12-24) mounted holes
- Toolless button holes to accept PDUs or cable managers

Package Includes

- SR4POST1224
- Installation hardware
- 50x pieces of 12-24 screws and washers
- Cable management hooks
- Owner's Manual with warranty information

Description

This 45U 4-Post Open Frame Rack with Threaded Mounting Holes helps IT managers organize their equipment and provides fast, easy access to installed IT equipment. The SR4POST1224 is a simple solution for housing IT equipment in secure environments and other areas that don't require a lockable rack solution. This 45U rack features heavy-duty cold-rolled steel construction with a black powder-coated finish for durability. It supports stationary loads up to 1,000 pounds (453.6 kilograms). The SR4POST1224 comes with all the hardware required for assembly and has a self-squaring design with bolt-down provisions. For high-density applications, multiple units can be bolted together side by side. The open design of the SR4POST1224 provides unobstructed airflow and easy access to equipment and cabling. It has threaded (12-24) mounting holes for easy installation of standard 19-inch rack equipment. The SR4POST1224 supports equipment depths from 22 to 36 inches. This rack also accommodates toolless button-hole mounting for vertical PDUs and cable managers.

Features

- Supports 1000 lbs (453.6 kgs) of rackmount equipment
- Adjustable mounting depth (22 to 36 inches)
- Textured powder coat finish
- Heavy-duty cold-rolled steel construction
- Numbered mounting positions
- Bolt down provisions
- Threaded 12-24 holes
- Black finish
- Easy assembly

Specifications

OVERVIEW	
UPC Code	037332159830
Device Compatibility	Patch Panel; Network Switch; UPS; Server



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

Rack Type	Open-Frame
PHYSICAL	
Color	Black
Rack Height	45U
Rack Depth	Standard
Maximum Device Depth (cm)	91.44
Maximum Device Depth (in.)	36
Maximum Device Depth (mm)	914
Minimum Device Depth (cm)	55.88
Minimum Device Depth (in.)	22
Minimum Device Depth (mm)	559
Shipping Dimensions (hwd / in.)	4.40 x 6.60 x 88.40
Shipping Dimensions (hwd / cm)	11.18 x 16.76 x 224.54
Shipping Weight (lbs.)	74.00
Shipping Weight (kg)	33.57
Unit Dimensions (hwd / in.)	84.300 x 20.300 x 39.400
Unit Dimensions (hwd / cm)	214.122 x 51.56 x 55.88 - 91.44
Unit Weight (lbs.)	69
Unit Weight (kg)	31.30
Weight Capacity - Stationary (kg)	454
Weight Capacity - Stationary (lbs.)	1000
Number of Vertical Mounting Rails	4
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Grounding Details	Includes a set of screws, bolts, and washers to secure a user-supplied grounding wire to Front and Back frames
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Certifications	IEC 60297-3
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SR4POST1224](#)