

Detachable PDU option with IEC output connections for compatible SmartOnline UPS Systems

MODEL NUMBER: **SUPDMB710IEC**



Description

The SUPDMB710IEC converts the output of our SmartOnline SU8000RT3U and SU10000RT3U to worldwide output connections. Manual bypass feature ensures maximum availability of connected equipment while UPS maintenance occurs. Can accept input voltages of 200-240 VAC. Hardwire input/ 6 IEC320 C19 output connections.

Features

- Converts the output of our SmartOnline SU8000RT3U and SU10000RT3U to worldwide output connections
- Manual bypass feature ensures maximum availability of connected equipment while UPS maintenance occurs
- Can accept input voltages of 200-240 VAC
- Hardwire input/ 6 IEC320 C19 output connections

Specifications

OVERVIEW	
UPC Code	037332143594
Accessory Type	PDU Module
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 230V AC; 240V AC; 220V AC
Input Connection Type	Hardwire
Voltage Compatibility (VAC)	200; 208; 220; 230; 240

Highlights

- Converts compatible SmartOnline high-voltage UPS systems to provide worldwide compatible output connections
- For use with input voltages of 200-240 VAC
- Hardwired input/ 6 IEC320 C19 output connections
- Manual bypass feature ensures maximum equipment availability

System Requirements

- For use with SmartOnline SU8000RT3U and SU10000RT3U Rack/Tower UPS systems in applications requiring a detachable PDU with manual bypass

Package Includes

- SUPDMB710IEC detachable PDU
- Mounting hardware
- Owner's Manual with warranty instructions



Powering Business Worldwide



OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) C19
Output Nominal Voltage	200/208/220/230/240 VAC
Overload Protection	6 double-pole 20A circuit breakers
PHYSICAL	
Material of Construction	Metal
Shipping Dimensions (hwd / in.)	13.40 x 9.40 x 9.60
Shipping Dimensions (hwd / cm)	34.04 x 23.88 x 24.38
Shipping Weight (lbs.)	9.90
Shipping Weight (kg)	4.49
Unit Dimensions (hwd / in.)	10.250 x 7.500 x 6.500
Unit Dimensions (hwd / cm)	26 x 19.1 x 16.5
Unit Weight (lbs.)	7.9
Unit Weight (kg)	3.58
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); UL 1778
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SUPDMB710IEC](#)