

## Protect It! 10-Outlet Surge Protector, 8 ft. (2.43 m) Cord with Right-Angle Plug, 2395 Joules, Tel/DSL Protection, Black Housing

MODEL NUMBER: TLP1008TEL



Safeguard your PC, printer, scanner, router, modem and other small home electronics against dangerous surges, spikes and line noise. Built-in RJ11 jacks also protect your telephone, fax machine and modem from surges.

### Description

Perfect for your home or office workstation, the TLP1008TEL Protect It!® 10-Outlet Surge Protector features a surge protection rating of 2395 joules to defend your sensitive electronic components against even the strongest surges and spikes.

Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP1008TEL protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G). It also filters out electromagnetic interference (EMI) and radio frequency interference (RFI) that can disrupt your electronics and inflict hardware damage or data loss.

Your devices plug into 10 NEMA 5-15R outlets, four of which are widely spaced to accept bulky transformers without blocking adjacent outlets. Sliding safety covers block accidental contact with unused outlets. RJ11 jacks allow connection of telephone/fax/modem equipment, which is also protected from surges.

An integrated 15A circuit breaker protects all outlets and shuts down connected equipment in case of overload. Diagnostic LEDs confirm your wall outlet is properly grounded and your connected equipment is protected.

The 8-ft. (2.43 m) AC power cord allows the TLP1008TEL to reach distant outlets, while its right-angle NEMA 5-15P plug allows furniture and equipment to be placed flush against the wall to save space in your workstation. Keyhole slots incorporated into the bottom panel provide convenient wall or desk mounting options for the black plastic housing.

### Features

**2395-Joule Surge Protection for Home or Office Electronics** Protects your computer, printer, scanner, router, modem and other small home electronics against even the strongest surges and spikes  
**Recommended for any desktop, network or home electronics application requiring AC line protection** Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression  
**Filters out disruptive EMI/RFI line noise** that can cause equipment damage or data loss  
**Exceeds IEEE 587 Category A and B surge suppression specifications**

**10 Outlets Accept Wide Range of Electronic Devices** 10 NEMA 5-15R AC outlets accept most computers and peripherals  
 4 widely spaced outlets accommodate bulky transformers without blocking other outlets  
 Sliding safety covers block accidental contact with unused outlets

**Telephone/DSL Protection** RJ11 jacks (1 input/2 output) protect phone/fax/modem equipment from

### Highlights

- 10 NEMA 5-15R outlets, including 4 for bulky transformers
- 2395-joule surge protection rating
- Filters out threatening EMI/RFI line noise
- 15A resettable circuit breaker prevents dangerous overloads
- 8-ft. (2.43 m) AC power cord with right-angle NEMA 5-15P plug

### Package Includes

- TLP1008TEL Protect It! 10-Outlet Surge Protector, Black Housing
- RJ11 telephone cable, 6-ft. (1.83 m)
- Owner's manual



Powering Business Worldwide



surges and spikes Built-in splitter protects 2 devices sharing one line 6 ft. RJ11 telephone cable included

**Premium Safety Features** On/off switch provides one-touch control over connected equipment Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required Integrated 15A circuit breaker shuts down outlets in case of power overload Diagnostic LEDs confirm grounding and protection status at a glance Conforms to current UL 1449 3rd Edition safety standards

**Fits Effortlessly Into Your Workstation** 8-ft. (2.43 m) AC power cord with right-angle NEMA 5-15P plug allows furniture and equipment to be placed flush against the wall Keyhole slots on bottom panel provide convenient wall or desk mounting options Black plastic housing designed for long life

**Backed by Ultimate Lifetime Insurance** \$150,000 Ultimate Lifetime Insurance covers any connected components damaged by power surge (U.S., Canada and Puerto Rico only)

## Specifications

OVERVIEW	
UPC Code	037332119063
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	120000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	8
Right-Angle Plug	Yes
Input Cord Length (m)	2.44
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(10) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A resettable circuit breaker
Transformer Accommodation	(8) Yes
Outlet Orientation	Two rows of outlets, including 4 widely spaced for transformers
Right-Angle Outlets	No



Powering Business Worldwide

**TRIPP-LITE**  
by **EATON**

Outlet Safety Covers Detail	Includes built-in sliding outlet safety covers
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and two-position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	2395
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	400V - UL Verified
EMI / RFI Filtering	Up to 40 dB
Automatic Shut-Off	Yes
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
<b>PHYSICAL</b>	
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	108 mm
Outlets Measurement (Center to Center)	Between Standard Outlets = 28.4mm; Between Standard and Transformer Outlets = 56.8mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	14.30 x 1.75 x 8.20
Shipping Dimensions (hwd / cm)	36.32 x 4.44 x 20.83
Shipping Weight (lbs.)	2.40
Shipping Weight (kg)	1.09
Unit Dimensions (hwd / in.)	11.800 x 5.300 x 1.800
Unit Dimensions (hwd / cm)	30.48 x 13.33 x 5.08
Unit Weight (lbs.)	2
Unit Weight (kg)	0.91

FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 226.92 (Canada); CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; UL 1449; UL 497A; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP1008TEL](#)