

Conference Power Surge Protector - 4 NEMA 5-15R Outlets, USB-C & 3 USB-A Ports, Micro-USB, 8 ft. Cord

MODEL NUMBER: TLP48USBCUFO



Safely charges and powers up to 8 mobile devices, including laptops, during important workplace meetings and conferences.

Features

Keep Your Team's Devices Powered and Charged During Important Meetings

Workplace meetings involve a variety of devices – laptops, smartphones, tablets – to keep everyone coordinated and up to date with the information necessary to make important decisions. Guaranteeing those devices remain charged and powered is Conference Power Surge Protector. Rounded to ensure equal access to everyone at the table, this UL-certified surge protector delivers ample power and reliable protection to as many as eight mobile devices at the same time.

NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your laptops, projector, printer or other conference-table electronics into four NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. Each rotating outlet is located far enough apart from the others to accept bulky transformers without blocking adjacent outlets.

4 USB Ports Provide Plenty of Charging Power

One USB-C and three USB-A ports are available for charging your smartphones, tablets and other USB mobile devices. The USB-A ports share 4.8A of charging power, which is plenty for delivering ample power to demanding devices. The USB-C charging port supplies up to 3A on its own.

Keeps Your Smart Speaker Fully Powered and at Your Disposal

A center device cradle is specially designed to fit an Amazon Echo Dot, Google Nest Mini or other smart speaker that allows access to instant information, external team members or just a little light thinking music. A built-in Micro-USB cable keeps the speaker powered.

1080 Joules Safeguard Your Sensitive Electronics

This Protect It!® surge protector features a surge suppression rating of 1080 joules to defend your sensitive electronic components against even the strongest power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP48USBCUFO protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. This surge protector

Highlights

- 4 NEMA 5-15R rotating outlets designed to accommodate bulky transformers
- 1080 joules protect your valuable electronics against dangerous surges and spikes
- 4 USB ports supply power for fast charging of phones, tablets and other mobile devices
- Built-in Micro-USB cord powers Echo Dot, Nest Mini or other smart speaker
- Long 8 ft. cord with NEMA 5-15P plug gives you more options in placing the unit

Applications

- Keep vital mobile devices fully powered and charged during important conferences and meetings
- Protect laptops, tablets, smartphones and other valuable electronics against AC power surges and spikes
- Filter potentially damaging line noise to improve connected equipment's performance and lifespan
- Safeguard valuable data against damage stemming from unexpected surges

Package Includes

- TLP48USBCUFO Conference Power Surge Protector
- Owner's manual



Powering Business Worldwide



filters out disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Premium Safety Features Protect Your Valuable Equipment

The on/off switch provides one-touch control over all connected equipment. Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required. A green LED confirms your connected equipment is protected.

Versatile Surge Protector Provides Flexible Installation Options

An eight-foot cord with NEMA 5-15P plug is long enough to give you plenty of options for placing the unit away from a wall outlet.

Specifications

OVERVIEW	
UPC Code	037332259745
Device Compatibility	Phone; Tablet
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Plug Features	Right Angle (36D)
Input Cord Gauge Type	14 gauge
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	8
Right-Angle Plug	No
Input Cord Length (m)	2.44
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	15
Overload Protection	Yes (2-in-1 switch)
Transformer Accommodation	(4) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

Diagnostic LED Details	Yes
CHARGING	
Number of Charging Ports	4
Total Charging Watts	24
Charging Method	USB
Charging Port Type	(3) USB A (FEMALE); (1) USB C (FEMALE)
Charging Ports / Amps	(3) 2.4A; (1) 3A
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	500, 500, 600
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Gray
Mounting Holes or Slots	No
Receptacle Color	Gray
Shipping Dimensions (hwd / in.)	8.30 x 8.10 x 3.70
Shipping Dimensions (hwd / cm)	21.08 x 20.57 x 9.40
Shipping Weight (lbs.)	2.09
Shipping Weight (kg)	0.95
Unit Dimensions (hwd / in.)	7.720 x 7.060 x 1.900
Unit Dimensions (hwd / cm)	19.3 x 17.6 x 4.9
Unit Weight (lbs.)	1.87
Unit Weight (kg)	0.85

Input Cord Color	White
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); NOM (Mexico); UL 1449; UL 1363
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP48USBCUFO](#)