

# Protect It! 6-Outlet Surge Protector, 8 ft. (2.43 m) Cord, 990 Joules, Tel/Modem Protection, Gray Housing

MODEL NUMBER: TLP608TEL



## Highlights

- 6 outlets / 8-ft. cord
- 990 joule rating
- Modem/fax surge protection

## Package Includes

- TLP608TEL
- 6-ft. telephone cord
- Instruction manual with warranty information

## Features

- 990 joules AC surge suppression shields equipment from the strongest surges and line noise
- 6 AC outlets with room for 1 transformer plugs without blocking outlets covers computers and peripherals
- Phone line surge suppression protects both dialup and DSL modems, plus fax machines, cordless phones and more (pair of RJ11 jacks, 2 wire, 1 line, includes 6 ft phone cable)
- 8 foot AC line cable
- Built-in power switch and 15 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LEDs confirm surge suppression status
- Attractive gray suppressor housing with keyhole mounting tabs allow versatile placement options
- UL1449 3rd Edition Rated (500V all modes), UL1363 (Power Tap), UL497A (Communications), Meets FCC part 68 rules, cUL (Canada)
- Exceeds IEEE 587 category A & B surge suppression specifications
- \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

## Specifications

| OVERVIEW |              |
|----------|--------------|
| UPC Code | 037332166432 |
| INPUT    |              |



Powering Business Worldwide

**TRIPP-LITE**  
by **EAT•N**

|  |   |
|--|---|
| Nominal Input Voltage(s) Supported           | 120V AC   |
| Recommended Electrical Service               | 120V (110-125V)   |
| Input Cord Gauge Type                        | 14 gauge; SJT   |
| Input Cord Gauge (AWG)                       | 14  |
| Voltage Compatibility (VAC)                  | 120   |
| Maximum Surge Amps                           | 35500   |
| Input Plug Type                              | NEMA 5-15P  |
| Input Cord Details                           | SJT   |
| Input Cord Length (ft.)                      | 8   |
| Right-Angle Plug                             | No  |
| Input Cord Length (m)                        | 2.44  |
| Integrated Cord Clip                         | No  |
| <b>OUTPUT</b>                                |   |
| Frequency Compatibility                      | 60 Hz   |
| Output Receptacles                           | (6) 5-15R   |
| Circuit Breaker (amps)                       | 15  |
| Transformer Accommodation                    | (2) Yes   |
| Outlet Orientation                           | Single row  |
| Right-Angle Outlets                          | No  |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |   |
| Diagnostic LED(s)                            | Yes   |
| Switches                                     | Combination AC circuit breaker and 2 position red illuminated on/off power switch |
| Diagnostic LED Details                       | Built-in LED confirms suppressor "protection present" (green) status              |
| <b>SURGE / NOISE SUPPRESSION</b>             |   |
| AC Suppression Joule Rating                  | 990   |
| AC Suppression Response Time                 | < 1 ns  |
| Protection Modes                             | Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression      |
| UL1449 Let Through Rating                    | 500V  |
| EMI / RFI Filtering                          | Up to 20 dB   |
| Automatic Shut-Off                           | Yes   |
| <b>DATALINE SURGE SUPPRESSION</b>            |   |
| Telephone/DSL Protection Details             | 1 line  |
| Cable (Coax) Protection                      | No  |



Powering Business Worldwide



|  |   |
|--|---|
| Network (Ethernet) Protection                              | No  |
| Telephone/DSL Protection                                   | Yes   |
| <b>PHYSICAL</b>  |   |
| Material of Construction                                   | Plastic   |
| Power Cord Color   | Light Gray  |
| Housing Color  | Light Gray  |
| Mounting Holes or Slots                                    | Yes   |
| Slot or Hole Mount Measurement (Center to Center)          | Distance between slots = 101 mm; Distance between slot height = 28 mm   |
| Outlets Measurement (Center to Center)                     | 28.5mm  |
| Receptacle Color   | Gray  |
| Shipping Dimensions (hwd / in.)                            | 13.20 x 2.00 x 5.90   |
| Shipping Dimensions (hwd / cm)                             | 33.53 x 5.08 x 14.99  |
| Shipping Weight (lbs.)                                     | 1.50  |
| Shipping Weight (kg)                                       | 0.68  |
| Unit Dimensions (hwd / in.)                                | 10.800 x 1.850 x 1.230  |
| Unit Dimensions (hwd / cm)                                 | 27.43 x 4.70 x 3.12   |
| Unit Weight (lbs.)   | 1.12  |
| Unit Weight (kg)   | 0.51  |
| <b>FEATURES &amp; SPECIFICATIONS</b>                       |   |
| Rotatable Outlets  | No  |
| Antimicrobial  | No  |
| <b>STANDARDS &amp; COMPLIANCE</b>                          |   |
| Product Certifications                                     | CAN/CSA-C22.2 No. 226.92 (Canada); CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; UL 1449; UL 497A; UL 1363; UL Listed |
| Product Compliance   | RoHS  |
| <b>WARRANTY &amp; SUPPORT</b>                              |   |
| Product Warranty Period (Worldwide)                        | Lifetime limited warranty   |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$20,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>                               |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP608TEL](#)