


6-Outlet Surge Protector - French Type E Outlets, 220-250V AC, 16A, 1.8 m Cord, Type E Plug, White

MODEL NUMBER: TLP6F18



6-outlet surge protector safeguards your home/office electronics against dangerous surges, spikes and line noise.

Features

6-Outlet Surge Protector Safeguards Your Sensitive Electronics Against Power FluctuationsIdeal for your home or office workstation, this Protect It!® 6-outlet surge protector features a surge suppression rating of 250 joules and provides protection in line-to-neutral (L-N) mode to defend your sensitive electronic components against power surges and spikes.

French Type E Outlets Accept a Wide Range of Electronic DevicesPlug your PC, printer, scanner, router, modem, television, stereo receiver or other home/office electronics into six Type E outlets to protect them against dangerous surges, spikes and line noise. The 1.8-meter AC power cord with space-saving right-angle Type E plug helps you connect the surge protector to a wall outlet located behind furniture.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform BetterVarious electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. This surge protector filters out disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Premium Safety Features for Protecting Your Valuable EquipmentThe TLP6F18 features an on/off switch that provides one-touch control over all connected devices. A green LED confirms that your connected equipment is protected. In the event of an overload, a resettable 16-amp circuit breaker immediately shuts down the power strip to prevent equipment damage. The high-impact plastic housing is designed for the rigors of everyday use.

Specifications

OVERVIEW	
UPC Code	037332251527

Highlights

- 6 Type E outlets distribute power to appliances, tools, lighting and other electronics
- Right-angle Type E plug permits connection in confined or hard-to-reach spaces
- 250 joules protect your valuable electronics against dangerous surges and spikes
- 44.5 cm plastic housing designed to withstand the rigors of everyday use
- 16A circuit breaker shuts down all outlets for safety in case of overload

Applications

- Protect computers, peripherals, home theater equipment and other valuable electronics against AC power surges and spikes
- Filter potentially damaging line noise to improve connected equipment's performance and lifespan
- Safeguard valuable data against damage stemming from unexpected surges

Package Includes

- TLP6F18 6-Outlet Surge Protector, French Type E Outlets, White



Powering Business Worldwide



INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250
Maximum Surge Amps	250
Input Plug Type	French
Right-Angle Plug	Yes
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) French/Belgian
Circuit Breaker (amps)	16
Overload Protection	combo switch/circuit breaker
Outlet Orientation	right-angled
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Two position power switch
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	250
Protection Modes	Includes full normal mode (H-N)
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	White
Housing Color	White
Mounting Holes or Slots	Yes
Receptacle Color	White



Powering Business Worldwide



Shipping Dimensions (hwd / in.)	18.00 x 3.40 x 2.90
Shipping Dimensions (hwd / cm)	45.72 x 8.64 x 7.37
Shipping Weight (lbs.)	1.50
Shipping Weight (kg)	0.68
Unit Dimensions (hwd / in.)	17.500 x 2.900 x 2.000
Unit Weight (lbs.)	1
Unit Weight (kg)	0.45
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP6F18](#)