

## 6-Outlet Surge Protector with 2 USB Ports (3.4A Shared) - Side Load, Direct Plug-In, 1050 Joules

MODEL NUMBER: TLP6SLUSBB



6-outlet surge protector with USB charging safeguards your home/office electronics against dangerous surges, spikes and line noise.

### Features

**6-Outlet Surge Protector with USB Charging Safeguards Your Sensitive Electronics** Ideal for your home or office workstation, this Protect It!® 6-outlet side-load surge protector features a surge protection rating of 1050 joules to defend your sensitive electronic components against strong power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP664USBB protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

**Side-Facing NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices** Plug your PC, printer, scanner, router, modem, television, stereo receiver and other home/office electronics into six NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. The TLP6SLUSBB plugs directly into a wall outlet (no cord required), and three outlets are included on either side. This allows you to install the surge protector behind furniture and other tight spaces without equipment power cords getting in the way. It's small enough to take with you for plugging in devices at the office or on the road.

**2 USB Ports Share 3.4 Amps of Charging Power** Two front USB-A ports are available for charging your smartphone, tablet and other USB mobile devices. They share 3.4A for charging two devices at the same time.

**Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better** Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. This surge protector filters out disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

**Includes the Latest Safety Features** An integrated 15A circuit breaker protects all outlets and automatically cuts power if the protection circuit is incapacitated, preventing equipment damage and indicating replacement is required. Diagnostic LEDs confirm your wall outlet is properly grounded and your connected equipment is protected. The TLP664USBB, with a high-impact black plastic housing, conforms to current UL 1449 4th Edition and cUL (Canada) safety standards.

## Specifications

### Highlights

- 6 side-facing NEMA 5-15R outlets allow convenient connection behind furniture
- 1050 joules protect your valuable electronics against dangerous surges and spikes
- 2 USB ports share 3.4A for fast charging of phones, tablets and other mobile devices
- Plugs directly into the wall (no cord required) for easy installation in tight spaces
- LEDs reassure you at a glance that your outlet is grounded and electronics are protected

### Applications

- Protect computers, peripherals, home theater equipment and other valuable electronics against AC power surges and spikes
- Filter potentially damaging line noise to improve connected equipment's performance and lifespan
- Safeguard valuable data against damage stemming from unexpected surges
- Charge smartphones, tablets or other USB devices via USB ports

### Package Includes

- TLP6SLUSBB Protect It! 6-Outlet Surge Protector, Side Load, Direct Plug-In, Black



Powering Business Worldwide

**TRIPP-LITE**  
by **EAT•N**

OVERVIEW	
UPC Code	037332239549
Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Length Details	Direct plug-in
Voltage Compatibility (VAC)	120
Maximum Surge Amps	60000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Built-in LEDs confirm suppressor "protected" (green) and "grounded" (red) status
CHARGING	
Number of Charging Ports	2
Total Charging Amps	3.4A
Total Charging Watts	17
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(2) 3.4A
Overcharge Protection	No



Powering Business Worldwide

**TRIPP-LITE**  
by **EAT•N**

SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1050
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	500, 500, 500
EMI / RFI Filtering	150 kHz to 100 mHz
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	5.30 x 3.40 x 2.80
Shipping Dimensions (hwd / cm)	13.46 x 8.64 x 7.11
Shipping Weight (lbs.)	0.75
Shipping Weight (kg)	0.34
Unit Dimensions (hwd / in.)	4.800 x 3.300 x 1.700
Unit Weight (lbs.)	0.5
Unit Weight (kg)	0.23
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); cUL Listed; UL 1449; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide



Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>
---	---

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP6SLUSBB](#)