

Protect It! 7-Outlet Surge Protector, 7 ft. (2.13 m) Cord, 1080 Joules, Tel/Modem Protection, Silver Housing

MODEL NUMBER: TLP707TEL



Highlights

- 7 outlets / 7-ft. (2.13 m) cord
- 1080 joule rating
- 1 in/1 out tel/modem surge protection

Package Includes

- TLP707TEL surge suppressor
- 6-ft. (1.83 m) RJ11 cable
- Instruction manual and warranty information

Description

TLP707TEL surge suppressor offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Heavy-grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more. TLP707TEL offers seven total outlets, seven-foot (2.1 meters) cord with space-saving angled plug, automatic cord management and diagnostic LEDs to warn of wiring problems and suppressor damage. Heavy-grade AC suppression rated at 1080 joules shields equipment from surges and line noise. Attractive metallic silver housing with three designated transformer plug outlets offers convenient protection of desktop computer equipment and accessories.

Features

- Offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics
- Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges
- Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more
- 7 total outlets
- 7-ft. (2.13 m) cord with space-saving angled plug, automatic cord management
- Diagnostic LEDs to warn of wiring problems and suppressor damage
- Heavy grade AC suppression rated at 1080 joules shields equipment from surges and line noise
- Attractive metallic silver housing
- 3 designated transformer plug outlets offer convenient protection of desktop computer equipment and accessories
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332119056
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	72000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	7
Right-Angle Plug	Yes
Input Cord Length (m)	2.13
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(7) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A resettable combo switch / circuit breaker
Transformer Accommodation	(5) Yes
Outlet Orientation	Two rows of outlets, 3 widely spaced on one side for transformers, 4 closely spaced outlets on the other
Right-Angle Outlets	No
Outlet Safety Covers Detail	Includes built-in sliding outlet safety covers
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	400V



Powering Business Worldwide



EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Black
Form Factors Supported	Supports floor / desktop placement
Housing Color	Black; Gray
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	Transformer Side Spacing = 61.8mm; Standard Outlet Side Spacing = 25.4mm
Receptacle Color	Silver
Shipping Dimensions (hwd / in.)	12.50 x 4.80 x 2.10
Shipping Dimensions (hwd / cm)	31.75 x 12.19 x 5.33
Shipping Weight (lbs.)	1.50
Shipping Weight (kg)	0.68
Unit Dimensions (hwd / in.)	1.970 x 1.610 x 10.910
Unit Dimensions (hwd / cm)	5.00 x 4.09 x 27.71
Unit Weight (lbs.)	1.25
Unit Weight (kg)	0.57
Input Cord Color	Black
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 1363; UL Listed
Product Compliance	FCC Part 68; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide



Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance
---	--

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP707TEL](#)