



Powering Business Worldwide

TRIPP LITE  
SERIES

## Protect It! 7-Outlet Surge Protector, 25 ft. Cord, 1080 Joules, Diagnostic LED, Light Gray Housing

MODEL NUMBER: TLP725



Safeguard your computer, printer, scanner, router, modem and other small home electronics against dangerous surges, spikes and line noise.

### Description

Perfect for your home or office workstation, the TLP725 Protect It!® 7-Outlet Surge Protector features a surge protection rating of 1080 joules to defend your sensitive electronic components against strong surges and spikes.

Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP725 protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G). It also filters out electromagnetic interference (EMI) and radio frequency interference (RFI) that can disrupt your electronics and inflict hardware damage or data loss.

Your devices plug into seven NEMA 5-15R outlets, one of which is spaced apart to accept a bulky transformer without blocking adjacent outlets. An integrated 15A circuit breaker protects all outlets and shuts down connected equipment in case of overload. The lighted on/off switch provides one-touch control over connected equipment. A diagnostic LED confirms your connected equipment is protected.

The extra-long 25-foot (7.6-meter) AC power cord with NEMA 5-15P plug gives you flexibility to reach distant outlets while fitting easily into your workstation or home theater setup. Keyhole slots incorporated into the bottom panel provide convenient wall or desk mounting options for the light gray plastic housing.

### Features

**1080-Joule Surge Protection for Home or Office Electronics** Protects your computer, printer, scanner, router, modem and other small home electronics against even the strongest surges and spikes  
Recommended for any desktop, network or home electronics application requiring AC line protection  
Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression  
Filters out disruptive EMI/RFI line noise that can cause equipment damage or data loss  
Exceeds IEEE 587 Category A and B surge suppression specifications

**7 Outlets Accept Wide Range of Electronic Devices** 7 NEMA 5-15R AC outlets accept most computers and peripherals  
Special end outlet designed for bulky transformers without blocking other outlets

**Premium Safety Features** Lighted on/off switch provides one-touch control over connected equipment  
Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required  
Diagnostic LED confirms protection status at a glance  
Conforms to current UL 1449 3rd Edition safety standards  
ABS fire retardant plastic case provides extra safety and durability

**Fits Effortlessly Into Your Workstation** Extra-long 25 ft. AC power cord with NEMA 5-15P plug reaches distant outlets  
Keyhole slots on bottom panel provide convenient wall or desk mounting options

### Highlights

- 7 NEMA 5-15R outlets—one designed for a bulky transformer
- 1080-joule surge protection rating
- Filters out threatening EMI/RFI line noise
- 15A resettable circuit breaker prevents dangerous overloads
- 25 ft. AC power cord with NEMA 5-15P plug

### Package Includes

- TLP725 Protect It! 7-Outlet Surge Protector, Light Gray Housing
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

**Backed by Ultimate Lifetime Insurance** \$25,000 Ultimate Lifetime Insurance covers any connected components damaged by power surge (U.S., Canada and Puerto Rico only)

## Specifications

OVERVIEW	
UPC Code	037332138316
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	72000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	25
Right-Angle Plug	No
Input Cord Length (m)	7.62
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(7) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and illuminated on/off power switch
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns



Powering Business Worldwide

TRIPP LITE  
SERIES

Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	Yes
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Material of Construction	Plastic
Power Cord Color	Gray
Housing Color	Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between slots = 151 mm; Distance between slot height = 24 mm
Outlets Measurement (Center to Center)	Distance between standard outlets = 29mm; Distance between last standard outlet and transformer outlet = 33mm
Receptacle Color	White
Shipping Dimensions (hwd / in.)	2.40 x 6.50 x 14.00
Shipping Dimensions (hwd / cm)	6.10 x 16.51 x 35.56
Shipping Weight (lbs.)	3.32
Shipping Weight (kg)	1.51
Unit Dimensions (hwd / in.)	1.320 x 2.050 x 11.690
Unit Dimensions (hwd / cm)	3.35 x 5.21 x 29.69
Unit Weight (lbs.)	3.04
Unit Weight (kg)	1.38
Input Cord Color	White
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 1363; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	



Powering Business Worldwide

TRIPP LITE  
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP725](#)