

## Protect It! 7-Outlet Surge Protector, 6 Right-Angle Outlets, 4 ft. (1.22 m) Cord, 1080 Joules, Diagnostic LED, Black Housing

MODEL NUMBER: TLP74RB



Safeguard your computer, printer, scanner, router, modem and other small home electronics against dangerous surges, spikes and line noise. Recommended for any desktop, network or home application requiring AC line protection.

### Features

**1080-Joule Surge Protection for Home or Office Electronics** Protects your computer, printer, scanner, router, modem and other small home electronics against surges and spikes Recommended for any desktop, network or home electronics application requiring AC line protection Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression Filters out disruptive EMI/RFI line noise that can cause equipment damage or data loss Exceeds IEEE 587 Category A and B surge suppression specifications

**7 Outlets Accept Wide Range of Electronic Devices** 6 NEMA 5-15R AC outlets placed at a right angle to simplify cord management Special end outlet designed for bulky transformers without blocking other outlets

**Premium Safety Features** Lighted on/off switch provides one-touch control over connected equipment Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required Diagnostic LED confirms protection status at a glance Conforms to current UL 1449 3rd Edition safety standards

**Fits Effortlessly Into Your Workstation** 4-ft. (1.22 m) AC power cord with NEMA 5-15P plug reaches nearby outlets Keyhole slots on bottom panel provide convenient wall or desk mounting options Black plastic housing designed for long life

**Backed by Ultimate Lifetime Insurance** \$25,000 Ultimate Lifetime Insurance covers any connected components damaged by power surge (U.S., Canada and Puerto Rico only)

### Highlights

- 6 right-angle NEMA 5-15R outlets (7 total)
- 1080-joule surge protection rating
- Filters out threatening EMI/RFI line noise
- 15A resettable circuit breaker prevents dangerous overloads
- 4 ft. AC power cord with NEMA 5-15P plug

### Package Includes

- TLP74RB Protect It! 7-Outlet Surge Protector, Black Housing
- Owner's manual

## Specifications

### OVERVIEW

UPC Code

037332155665



Powering Business Worldwide

TRIPP LITE  
SERIES

INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	4
Right-Angle Plug	No
Input Cord Length (m)	1.22
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(7) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(4) Yes
Outlet Orientation	Single row
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position on/off power switch
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Yes
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No



Powering Business Worldwide

TRIPP LITE  
SERIES

Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	No
Slot or Hole Mount Measurement (Center to Center)	300 mm
Outlets Measurement (Center to Center)	28.5mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	14.00 x 1.75 x 4.50
Shipping Dimensions (hwd / cm)	35.56 x 4.44 x 11.43
Shipping Weight (lbs.)	1.20
Shipping Weight (kg)	0.54
Unit Dimensions (hwd / in.)	1.330 x 2.040 x 12.400
Unit Dimensions (hwd / cm)	3.38 x 5.18 x 31.50
Unit Weight (lbs.)	1.04
Unit Weight (kg)	0.47
Input Cord Color	Black
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 1363; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000&nbsp;<a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp;



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP74RB](#)