

Protect It! 8-Outlet Surge Protector, 6 ft. (1.83 m) Cord, 2160 Joules, Tel/DSL Protection, Cord Clip

MODEL NUMBER: TLP806TEL



Highlights

- 8 outlets / 6-ft. cord
- 2160 joule rating
- Modem/fax surge protection

Package Includes

- TLP806TEL
- 6-ft. (1.83 m) telephone cord
- Instruction manual with warranty information

Description

The TLP806TEL surge suppressor has eight outlets, a six-foot (1.8-meter) cord with a space-saving right-angle plug and diagnostic LEDs. The unit has a surge suppression rating of 2160 joules to handle the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment.

Features

- 2160 joules AC surge suppression shields equipment from the strongest surges and line noise
- 8 AC outlets with room for 2 transformer plugs without blocking outlets covers computers and all peripherals
- Long 6-ft. (1.83 m) AC line cable with space-saving angle input plug conveniently reaches distant outlets
- Built-in RJ11 jacks (1 in/1 out) prevent surges from damaging your modem/fax/phone equipment
- Built-in cord management
- Lighted power switch with integrated 15 amp circuit breaker offers power control and overload protection
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive black suppressor housing with keyhole mounting tabs allow versatile placement options
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

| OVERVIEW | |
|------------------------------------|--------------|
| UPC Code | 037332175229 |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--|---|
| Recommended Electrical Service | 120V (110-125V) |
| Input Plug Features | Right Angle (90D) |
| Input Cord Gauge Type | 14 gauge; SJT |
| Input Cord Gauge (AWG) | 14 |
| Voltage Compatibility (VAC) | 120 |
| Maximum Surge Amps | 144000 |
| Input Plug Type | NEMA 5-15P |
| Input Cord Details | SJT |
| Input Cord Length (ft.) | 6 |
| Right-Angle Plug | Yes |
| Input Cord Length (m) | 1.83 |
| Integrated Cord Clip | Yes |
| OUTPUT | |
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (8) 5-15R |
| Circuit Breaker (amps) | 15 |
| Transformer Accommodation | (5) Yes |
| Outlet Orientation | Single row of 6, plus 2 for transformer accommodation |
| Right-Angle Outlets | No |
| Outlet Safety Covers Detail | Includes built-in sliding outlet safety covers |
| USER INTERFACE, ALERTS & CONTROLS | |
| Diagnostic LED(s) | Yes |
| Switches | Combination AC circuit breaker and 2-position red illuminated on/off power switch |
| Diagnostic LED Details | Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 2160 |
| AC Suppression Response Time | < 1 ns |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression |
| UL1449 Let Through Rating | 330/400/400 |
| EMI / RFI Filtering | Up to 40 dB |
| Automatic Shut-Off | Yes |
| DATALINE SURGE SUPPRESSION | |
| Telephone/DSL Protection Details | 1 line |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--|---|
| Cable (Coax) Protection | No |
| Network (Ethernet) Protection | No |
| Telephone/DSL Protection | Yes |
| PHYSICAL | |
| Material of Construction | Plastic |
| Power Cord Color | Black |
| Housing Color | Black |
| Mounting Holes or Slots | No |
| Slot or Hole Mount Measurement (Center to Center) | Distance between horizontal slots 101.35 mm = Distance between vertical slots = 30 mm |
| Outlets Measurement (Center to Center) | 29mm |
| Receptacle Color | Black |
| Shipping Dimensions (hwd / in.) | 2.50 x 5.20 x 13.30 |
| Shipping Dimensions (hwd / cm) | 6.35 x 13.21 x 33.78 |
| Shipping Weight (lbs.) | 1.70 |
| Shipping Weight (kg) | 0.77 |
| Unit Dimensions (hwd / in.) | 1.740 x 2.000 x 12.400 |
| Unit Dimensions (hwd / cm) | 4.42 x 5.08 x 31.5 |
| Unit Weight (lbs.) | 1.2 |
| Unit Weight (kg) | 0.54 |
| Input Cord Color | Black |
| FEATURES & SPECIFICATIONS | |
| Additional Information | Pair of phone line output jacks serve as a line splitter to enable the protection of two devices sharing a single dialup phone line |
| Rotatable Outlets | No |
| Antimicrobial | No |
| STANDARDS & COMPLIANCE | |
| Product Certifications | CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 1363; UL Listed |
| Product Compliance | FCC Part 68; RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$150,000 Ultimate Lifetime Insurance |



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP806TEL](#)