

8-Outlet Surge Protector with 4 USB Ports (4.2A Shared) - 6 ft. (1.83 m) Cord, 1800 Joules, Black

MODEL NUMBER: TLP864USBB



8-outlet surge protector safeguards your home/office electronics against dangerous surges, spikes and line noise.

Features

8-Outlet Surge Protector with USB Safeguards Your Sensitive Electronics Ideal for your home or office workstation, this Protect It!® 8-outlet surge protector features a surge protection rating of 1800 joules to defend your sensitive electronic components against even the strongest power surges and spikes.

NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices Plug your PC, printer, wireless router, game console, television, sound system or other home/office electronics into eight NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise.

Surge Protector with 4 USB Ports That Share 4.2 Amps of Charging Power Four USB-A ports are available for charging your smartphone, tablet and other USB mobile devices.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. This surge protector filters out disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Includes the Latest Safety Features The lighted on/off switch provides one-touch control over connected equipment. A green LED confirms your connected equipment is protected.

Versatile Surge Protector Provides Multiple Installation Options This surge protector with 6-ft. (1.83 m) cord and NEMA 5-15P plug allows you flexibility in placing the unit away from a wall outlet. Keyhole slots incorporated into the bottom panel provide convenient wall or desk mounting options for the black plastic housing.

Highlights

- 8 NEMA 5-15R outlets distribute AC power to connected home/office equipment
- 1800 joules protect your valuable electronics against dangerous surges and spikes
- 4 USB ports share 4.2A for fast charging of phones, tablets and other mobile devices
- 6-ft. (1.83 m) cord with NEMA 5-15P plug allows flexibility in placing devices away from AC outlet
- Green LED reassures you at a glance that your valuable electronics are protected

Applications

- Protect computers, peripherals, home theater equipment and other valuable electronics against AC power surges and spikes
- Filter potentially damaging line noise to improve connected equipment's performance and lifespan
- Safeguard valuable data against damage stemming from unexpected surges
- Charge smartphones, tablets or other USB devices via USB ports

Package Includes

- TLP864USBB Protect It! 8-Outlet Surge Protector, Black
- Owner's manual

Specifications

OVERVIEW



Powering Business Worldwide

TRIPP LITE
SERIES

UPC Code	037332223654
Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	35500
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A resettable illuminated combo switch / circuit breaker
Transformer Accommodation	(4) Yes
Outlet Orientation	Double row of 8 outlets
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status
CHARGING	
Number of Charging Ports	4
Total Charging Watts	21
Charging Method	USB



Powering Business Worldwide

TRIPP LITE
SERIES

Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(4) 4.2A
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1800
AC Suppression Response Time	< 1 ns
UL1449 Let Through Rating	800,800,800
EMI / RFI Filtering	Yes
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	Yes
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	11.02 x 6.69 x 1.65
Shipping Weight (kg)	0.75
Unit Dimensions (hwd / in.)	9.450 x 3.580 x 1.450
Unit Dimensions (hwd / cm)	3.72 x 1.14 x 0.57
Unit Weight (lbs.)	1.22
Unit Weight (kg)	0.55
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 497A; UL 1363; UL Listed
Product Compliance	FCC Part 68; RoHS



Powering Business Worldwide

TRIPP LITE
SERIES

WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP864USBB](#)