

USB Extension Cable (USB-A Right-Angle M to USB-A F), 10-in. (25.4 cm)

MODEL NUMBER: U005-10I



Highlights

- Modifies the cable connecting to a PC to 90 degrees
- 24k gold-plated connectors and gold-plated copper contacts
- 24 gauge power wires

System Requirements

- USB port and device

Package Includes

- USB 2.0 Gold Extension cable - USB "A" Right-Angle Male to USB "A" Female - 10"

Features

- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil feature twisted 28/24 AWG data lines
- Gold-plated connectors and gold-plated copper contacts provide superior conductivity
- Molded connectors with built-in strain relief ensure that the cable lasts a long time

Specifications

OVERVIEW	
UPC Code	037332117861
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB A (FEMALE)
Connector Style	Angled
PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	0.8
Cable Length (m)	0.24
Cable Length (in.)	10



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Length (cm)	25.40
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U005-10I](#)