

2-Port USB 2.0 Desktop Extension Cable (M/2xF), 5 ft. (1.52 m)

MODEL NUMBER: U024-005-DSK2



Converts your computer's USB-A port to 2 USB-A ports and extends them up to 5 ft away. Ideal for connecting thumb drives, digital cameras and other USB-A devices.

Features

Expands an Existing USB-A Port to 2 Ports and Extends Them an Extra 5 ft.

- Move a hard-to-reach USB port within easy access
- Ideal for connecting external hard drives, thumb drives, digital cameras and other USB-A devices
- Features one USB 2.0 data/power port and one power-only port
- Supports data transfer rates up to 480 Mbps
- Backward compatible with earlier USB generations

First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding for EMI/RFI noise protection
- Molded nickel-plated connectors for optimal signal quality
- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Flexible PVC jacket easy to install in tight spaces
- Black padded non-sliding base

Specifications

OVERVIEW	
UPC Code	037332199348
Technology	USB 2.0 (High Speed)
Cable Type	Passive

Highlights

- Features one USB 2.0 data/power port and one power-only port
- Supports data transfer rates up to 480 Mbps
- Premium foil and braid shielding
- Backward compatible with earlier USB generations
- Twisted 28/24 AWG data/power lines

System Requirements

- Computer, laptop or other device with USB-A port

Package Includes

- U024-005-DSK2 2-Port USB 2.0 Hi-Speed Desktop Extension Cable (M/2xF), 5 ft.



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

INPUT	
Maximum Input Amps	2
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	(2) USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
CHARGING	
Total Charging Watts	10
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5mm
Cable Length (ft.)	5
Cable Length (m)	1.52
Shipping Dimensions (hwd / in.)	5.31 x 3.94 x 0.50
Shipping Dimensions (hwd / cm)	13.49 x 10.01 x 1.27
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 131°F (-10° to 55°C)
Relative Humidity	5% to 90% RH, Non-Condensing
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	10W (5V/2A)
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)

Data Transfer Rate	480 Mbps
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U024-005-DSK2](#)