

## USB-C 60W Device Charging Cable (M/M) - USB 2.0, Black, 3 ft. (0.91 m)

MODEL NUMBER: U040-003-C



USB cable connects a smartphone or other USB-C device to the USB-C port on your computer, charger or power bank.

### Features

#### USB-C Cable Connects Devices for Charging

This USB cable (M/M) is compatible with any device with a USB-C or Thunderbolt 3 port, including MacBook Pros, Chromebooks and Windows laptops. It allows you to connect your notebook computer to a docking station, your Apple or Android device to a wall charger or power bank, or an external hard drive to a PC or tablet, to name just a few valuable uses for the cable.

#### PD Charging Cable Supports up to 60W for Syncing and Charging Mobile Devices

The Power Delivery cable provides power output up to 20V 3A (60W), which is sufficient for fast charging, syncing and powering most smartphones and other mobile devices. It also supports USB 2.0 data transfer rates up to 480 Mbps. The USB-C to USB-C cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

#### Reversible USB-C Connectors Attach in Either Direction

Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connectors plug into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time.

## Specifications

| OVERVIEW            |                      |
|---------------------|----------------------|
| UPC Code            | 037332263629         |
| Technology          | USB 2.0 (High Speed) |
| Cable Type          | Passive              |
| INPUT               |                      |
| Maximum Input Amps  | 3                    |
| Maximum Input Watts | 60                   |

### Highlights

- Power Delivery cable supports 20V 3A (60W) power output for charging host device
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient data transfers
- Reversible USB-C plugs connect in either direction for immediate no-fuss use
- USB-C to USB-C cable is compatible with all USB-C and Thunderbolt 3 devices

### System Requirements

Devices with USB-C or Thunderbolt 3 ports

### Package Includes

U040-003-C USB-C to USB-C Cable, M/M, Black, 3 ft. (0.9 m)



Powering Business Worldwide

TRIPP LITE  
SERIES

|  |                             |
|--|-----------------------------|
| Product Length (in.)                           | 39.4                        |
| Product Length (cm.)                           | 100                         |
| Product Length (ft.)                           | 3                           |
| Product Length (m)                             | 0.9                         |
| <b>POWER</b>                                   |                             |
| USB Power Delivery (PD) Charging Support       | Yes                         |
| USB Power Delivery (PD) Charging Specification | 60W                         |
| <b>CONNECTIONS</b>                             |                             |
| Side A - Connector 1                           | USB C (MALE)                |
| Side B - Connector 1                           | USB C (MALE)                |
| Connector Plating                              | Nickel                      |
| Contact Plating                                | Gold                        |
| Connector Style                                | Straight                    |
| <b>PHYSICAL</b>                                |                             |
| Material of Construction                       | PVC                         |
| Cable Jacket Color                             | Black                       |
| Cable Jacket Material                          | PVC                         |
| Cable Jacket Rating                            | VW-1                        |
| Cable Outer Diameter (OD)                      | 3.0MM                       |
| Cable Length (ft.)                             | 3                           |
| Cable Length (m)                               | 0.91                        |
| Cable Length (in.)                             | 36                          |
| Cable Length (cm)                              | 91.4                        |
| Shipping Dimensions (hwd / in.)                | 9.00 x 7.00 x 0.50          |
| Shipping Dimensions (hwd / cm)                 | 22.86 x 17.78 x 1.27        |
| Shipping Weight (lbs.)                         | 0.06                        |
| Shipping Weight (kg)                           | 0.03                        |
| Unit Dimensions (hwd / in.)                    | 9.000 x 7.000 x 0.500       |
| Unit Packaging Type                            | Polybag                     |
| <b>ENVIRONMENTAL</b>                           |                             |
| Operating Temperature Range                    | 14° to 140°F (-10° to 60°C) |
| Storage Temperature Range                      | -4° to 158°F (-20° to 70°C) |
| Operating Humidity Range                       | 10% to 85%, Non-Condensing  |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                       |                            |
|---------------------------------------|----------------------------|
| Storage Humidity Range                | 10% to 85%, Non-Condensing |
| Power Provided to Connected Device(s) | 60W (20V/3A)               |
| <b>FEATURES &amp; SPECIFICATIONS</b>  |                            |
| USB Specification                     | USB 2.0 (up to 480 Mbps)   |
| <b>STANDARDS &amp; COMPLIANCE</b>     |                            |
| Product Compliance                    | RoHS; REACH                |
| <b>WARRANTY &amp; SUPPORT</b>         |                            |
| Product Warranty Period (Worldwide)   | Lifetime limited warranty  |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U040-003-C](#)