

USB 5-Pin Mini-B to USB-C Cable - USB 2.0, (M/M), 6 ft. (1.83 m)

MODEL NUMBER: **U040-006-MINI**



Connect devices with a 5-Pin Mini-B connector to the USB Type-C (USB-C) port on your tablet, laptop, ultrabook or computer

Features

- 6-ft. USB 2.0 5-Pin Mini-B Male to USB Type-C (USB-C) Male cable
- USB Type-C connector is reversible, so there is no guessing on which way to plug it in.....it connects in either direction!
- Supports USB 2.0 data transfer rates up to 480Mbps
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 28AWG Data Pair / 20AWG Power pair; Supports 500mA current

Specifications

OVERVIEW	
UPC Code	037332188601
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB MINI-B 5-PIN (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight

Highlights

- 6-ft. USB 2.0 5-Pin Mini-B Male to USB Type-C (USB-C) Male cable
- USB Type-C connector is reversible, so there is no guessing on which way to plug it in
- Supports USB 2.0 data transfer rates up to 480Mbps

System Requirements

- A device with a 5-Pin Mini-B connector
- A tablet, laptop, ultrabook or computer with a USB Type-C (USB-C) port.

Package Includes

- USB 2.0 5-Pin Mini-B Male to USB Type-C (USB-C) Male Cable - 6-ft.



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.5MM
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.09
Shipping Weight (kg)	0.04
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	10% to 85%, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U040-006-MINI](#)