


Safe-IT USB-C Cable (M/M), Antibacterial, Ultra Flexible, 240W PD Charging, Light Blue, 6 ft. (1.8 m)

MODEL NUMBER: U040AB-006CS5LB



USB-C cable with antibacterial material provides up to 240W for powering and charging a MacBook Pro via USB-C charger or power bank.

Features

USB-C Cable Connects Devices for Charging or Transferring Data

This USB cable (M/M) is compatible with any device with a USB-C or Thunderbolt 3 port, including a MacBook Pro, iPad, iMac, Chromebook or Windows laptop. It allows you to connect your notebook computer to a docking station, your Apple or Android device to a wall charger or power bank, or an external hard drive to a PC or tablet.

Innovative Soft Cable Jacket Prevents Tangles, Allows Flexible Bends

Very flexible for convenient on-the-go connections, this ultra-soft silicone-layered jacket avoids nasty tangles in your backpack or laptop bag and feels nice to the touch. Plus, it bends easily for connecting to devices in tight spaces or around obstacles.

PD Charging Cable Supports up to 240W for Syncing and Charging Mobile Devices

The Power Delivery cable provides power output up to 48V 5A (240W), more than sufficient for fast charging, syncing and powering most large-capacity devices, including the MacBook Pro. It is backward compatible with lower wattages, including 100W and 60W, and will communicate with the connected device to determine what level of power can be supported. This USB-C to USB-C cable also supports USB 2.0 data transfer rates up to 480 Mbps.

Provides Extra Protection Against Certain Bacteria

The molded connectors and jacket are constructed using an antibacterial material that is effective in inhibiting *Escherichia coli* (E. coli) and *Staphylococcus aureus* (staph). This added protection makes this Safe-It™ cable an ideal solution for medical facilities, schools, businesses, restaurants/kitchens and anywhere else that needs extra protection against bacteria.

Light Blue Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The USB cable has a light blue jacket, which is easy to identify quickly in a crowded docking station or USB hub and helps prevent the cable from becoming accidentally disconnected.

Specifications

Highlights

- Soft, flexible silicone jacket allows easy bending and avoids messy tangling
- Constructed with antibacterial material proven effective in inhibiting E. coli and staph
- Power Delivery cable supports 5A (240W) for fast-charging large-capacity devices
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient charges and data transfers
- Light blue jacket permits fast, easy identification in a crowded docking station or hub

System Requirements

Devices with USB-C or Thunderbolt 3 ports

Package Includes

U040AB-006CS5LB USB-C to USB-C Cable (M/M), Light Blue, 6 ft. (1.8 m)



Powering Business Worldwide

TRIPP LITE
SERIES

OVERVIEW	
UPC Code	037332276797
Technology	USB 2.0 (High Speed)
Cable Type	Passive
INPUT	
Maximum Input Amps	5
Maximum Input Watts	240
POWER	
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	3.1
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Nickel
Connector Style	Straight
PHYSICAL	
Material of Construction	Silicone
Cable Jacket Color	Light Blue
Connector Color	Light Blue
Cable Jacket Material	TPE
Cable Jacket Rating	FT2
Cable Outer Diameter (OD)	5.0MM
Wire Gauge (AWG)	30/29/22
Cable Length (ft.)	6.6
Cable Length (m)	2.01
Cable Length (in.)	78.7
Cable Length (cm)	91.4
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.17
Shipping Weight (kg)	0.08



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	14° to 140° F (-10° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 85%, Non-Condensing
Storage Humidity Range	10% to 85%, Non-Condensing
Power Provided to Connected Device(s)	240W (48V/5A)
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Antibacterial	Yes
IP68 Rated	No
Angled Plug	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 94
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U040AB-006CS5LB](#)