

10-Port USB Charging Station with Adjustable Storage, 12V 8A (96W) USB Charger Output, Schuko Power Cord

MODEL NUMBER: U280-010-ST-CEE



10-port USB charger keeps electronic devices, including smartphones, earbuds and smart watches, e-readers, and Micro-USB tablets at full capacity via USB connection. Neatly organizes the devices within its adjustable storage brackets while charging.

Description

Whether you're at home or in the office, the U280-010-ST-CEE 10-Port USB Charging Station provides plenty of ports and power to keep all your devices at 100% capacity. No more peering behind furniture to find an available outlet or unplugging one device to charge another. You can charge up to ten smartphones, Micro-USB tablets, e-readers, and other devices at the same time. This charging station for multiple devices doesn't require a computer, so you can take it anywhere AC power is available. To charge your USB devices, simply plug the included external dual-voltage (100V–240V) power supply into a Schuko outlet, and connect your devices to the available USB ports. The charger protects against overheating, overcurrent and overcharging—in fact, it stops charging as soon as your devices' batteries are at full capacity. A front LED indicates the unit is turned on and receiving AC power. The 10-port USB charger supports USB Battery Charging (BC) specification v1.2 and delivers up to 5V 2.4A to each port, which is plenty for charging even battery-intensive devices. Adjustable brackets on top of the charger act as storage, providing space to neatly organize devices while they charge. You can adjust the brackets to accommodate the number and size of the devices being charged.

Features

Charges Up to 10 Devices at the Same Time Ideal for charging smartphones, Micro-USB tablets, e-readers, earbuds and smartwatches, and other devices at home or work Connect devices to unit's USB ports for proficient charging Charges anywhere AC power is available—no computer required

Provides Plenty of Juice for Charging Delivers up to 5V 2.4A per port to charge battery-intensive devices Complies with USB Battery Charging (BC) specification v1.2 Protects against overheating, overcurrent and overcharging

Also Functions as Efficient Storage Includes 14 adjustable brackets that neatly organize devices while they charge Brackets are adjustable to accommodate number and size of devices being charged

Easy to Use Included external dual-voltage (100–240V) power supply plugs into a Schuko outlet Front LED indicates when unit is turned on and receiving AC power

Highlights

- Up to 5V 2.4A per port for charging battery-intensive devices
- All ten ports support USB Battery Charging (BC) specification v1.2
- External dual-voltage power supply with Schuko plug
- Protects against overheating, overcurrent and overcharging
- Includes 14 adjustable storage brackets for organizing devices
- Charges anywhere AC power is available—no computer required (for 120V applications please use P013-Series cables, not included)

Package Includes

- U280-010-ST-CEE 10-Port USB Charging Station
- External Power Supply (Input: 100–240V, 50/60 Hz, 2A; Max Output: 12V 8A)
- C5 to CEE 7/7 Schuko Power Cord - 3-ft.
- (14) Storage brackets
- Owner's manual

Specifications



Powering Business Worldwide

TRIPP LITE
SERIES

| OVERVIEW | |
|---|--|
| UPC Code | 037332205698 |
| Product Type | Charging Station |
| Charging Form Factor | Charging Hub |
| Device Compatibility | Amazon Kindle; Headphones; Phone; Tablet; Watch |
| INPUT | |
| AC Power Adapter Plug(s) | CEE 7/7 Schuko |
| AC Power Adapter Input Specs (V / Hz / A) | 100-240V / 50/60Hz / 3A |
| AC Power Adapter Output Specs (V / A) | 12V / 8A |
| AC Power Adapter Cord Length (ft.) | 3 |
| AC Power Adapter Cord Length (m) | 1 |
| Nominal Input Voltage(s) Supported | 120V AC; 230V AC |
| Input Connection Type | USB-A Female |
| Voltage Compatibility (VAC) | 100; 110; 120; 125; 127; 200; 208; 220; 230; 240 |
| Input Plug Type | CEE 7/7 Schuko |
| OUTPUT | |
| Overload Protection | Yes |
| POWER | |
| Power Source Type | AC Adapter |
| AC Adapter | Input: 100-240V, 50/60Hz, 3.0A; Output: 12V, 8A, 3-ft. |
| DC Barrel Plug | OD: 5.5 x 2.5 x 10mm, Positive Pin, Negative Sleeve |
| Power Consumption (Watts) | 34 |
| Power Consumption Detail | 34W (Operating) 0.27W (Standby) |
| CONNECTIONS | |
| Number of Ports | 10 |
| Side A - Connector 1 | CEE 7/7 SCHUKO PLUG |
| Side B - Connector 1 | (10) USB A (MALE) |
| USER INTERFACE, ALERTS & CONTROLS | |
| LED Indicators | Power (Blue) |
| CHARGING | |
| Number of Charging Ports | 10 |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--------------------------------------|--------------------------------------|
| Total Charging Amps | 8A |
| Total Charging Watts | 96 |
| Charging Method | USB |
| Charging Method Detail | 5V - 1.5A (7W) |
| Charging Port Type | (10) USB A (FEMALE) |
| Charging Ports Details | USB-A: 12V/8A |
| Charging Ports / Amps | (10) 2.4A |
| PHYSICAL | |
| Color | Black |
| Material of Construction | Polycarbonate |
| Unit Dimensions (hwd / in.) | 1.000 x 9.400 x 4.700 |
| Unit Dimensions (hwd / cm) | 2,5 x 23,8 x 11,8 |
| Unit Packaging Type | Box |
| Unit Weight (lbs.) | 0.66 |
| Unit Weight (kg) | 0.30 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 41° to 95°F (5° to 35°C) |
| Storage Temperature Range | -4° to 122°F (-20° to 50°C) |
| Relative Humidity | 20% to 80% RH, Non-Condensing |
| FEATURES & SPECIFICATIONS | |
| GaN Technology | No |
| Overcurrent Protection | Yes |
| Overvoltage Protection | Yes |
| Quick Charge Compliant | No |
| IP68 Rated | No |
| IP20 Rated | No |
| Driver Required | No |
| STANDARDS & COMPLIANCE | |
| External Power Supply Certifications | CE; FCC; UL; TUV; CCC; PSE; GS; RoHS |
| Product Compliance | RoHS; CE (Europe); REACH; FCC (USA) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U280-010-ST-CEE](#)