

## USB 3.0 SuperSpeed Device Cable (A to Micro-B M/M), Blue, 3 ft. (0.91 m)

MODEL NUMBER: U326-003



Connects a USB3.0 enabled computer to a USB3.0 peripheral with Micro-B type connector

### Description

This USB-A to Micro-B SuperSpeed USB 3.0 cable brings significant performance enhancements to the ubiquitous USB standard, while remaining compatible with the billions of USB-enabled devices currently deployed in the market. SuperSpeed USB will deliver 10 times the data transfer rate of Hi-Speed USB, up to 5 Gbps, as well as improved power efficiency. USB 3.0 utilizes a bi-directional data interface rather than USB 2.0's half-duplex arrangement, where data can only flow in one direction at a time, giving a ten-fold increase in theoretical bandwidth.

### Features

- 3-ft. (0.91 m) USB 3.0 SuperSpeed A-Male to Micro-B Male
- SuperSpeed USB is 10 times faster than Hi-Speed USB, with transfer rates up to 5 Gbps.
- SuperSpeed USB is a Sync-N-Go technology that minimizes user wait-time.
- SuperSpeed USB will provide Optimized Power Efficiency...No device polling and lower active and idle power requirements.
- SuperSpeed USB is backwards compatible with USB 2.0. Devices interoperate with USB 2.0 platforms. Hosts support USB 2.0 legacy devices.

## Specifications

OVERVIEW	
UPC Code	037332158123
Technology	USB 3.x
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 MICRO-B (MALE)

### Highlights

- 3-ft. (0.91 m) SuperSpeed USB 3.0 A to Micro-B Cable
- 10 times faster than USB 2.0, with transfer rates up to 5 Gbps

### System Requirements

- Computers and Peripherals with USB 3.0 capabilities

### Package Includes

- 3-ft. (0.91 m) USB 3.0 SuperSpeed A-Male to Micro-B Male



Powering Business Worldwide

TRIPP LITE  
SERIES

Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
<b>PHYSICAL</b>	
Material of Construction	PVC
Cable Jacket Color	Blue
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.5MM
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.10
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 0.25
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	10% to 85%, Non-Condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps)
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U326-003](#)