

HDMI to USB Video Capture Adapter, 4K 60 Hz, USB 3.2 Gen 1, TAA

MODEL NUMBER: U444-H4K6-CAP



Captures 4K video from an HDMI device and sends it to a PC or laptop for streaming or editing.

Features

Captures 4K Video from One Device and Sends It to a Second Device for Streaming or Editing

This bus-powered video capture adapter allows you to record 4K video from an HDMI source, such as a webcam, cable/satellite box, gaming console, security camera or media center. Then, you can transmit that 4K video to your computer or laptop's USB-A port for editing or real-time streaming to an audience. The U444-H4K6-CAP is recommended for office presentations, workplace meetings, online game streaming, podcasts and video productions.

Compatible with a Wide Range of Popular Video Applications

The U444-H4K6-CAP lets you record conference calls, presentations, security feeds, training videos and more using third-party software, including Microsoft Teams, Zoom, Twitch and GoToMeeting. You can edit video using VLC or OBS (among other software) and release it through YouTube and other content-sharing sites. This adapter also works with Google Hangouts and Adobe Connect. It supports USB Video Content (UVC) and USB Audio Content (UAC) for driver-free usage with both Windows and macOS computers.

Transmits 4K Video with HDR and 4:4:4 Color

The U444-H4K6-CAP supports Ultra HD 4K resolutions up to 3840 x 2160 at 60 Hz. It supports HDR (High Dynamic Range), providing a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.3 encryption allows you to stream 4K content with no complications. This adapter also supports uncompressed 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor. **Note:** The maximum video output resolution is determined by the video specifications of the host device and HDMI cable connected to the adapter.

Simple to Set Up and Use

This lightweight video adapter is bus-powered for traveling between conference rooms or conducting on-site training and video recordings. The plug-and-play U444-H4K6-CAP requires no external power or extra software. Just connect the HDMI port to a video camera or other host device with a user-supplied HDMI cable, and connect the USB-A port to a laptop or computer with a user-supplied USB cable.

Highlights

- Ideal for work presentations, online gaming, podcasts and video productions
- Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) with High Dynamic Range (HDR)
- Compatible with Microsoft Teams, Zoom, VLC and other popular video applications
- Bus-powered via host's USB-A port, so no external power supply is needed
- Plug-and-play operation with no software required for easy, immediate installation

System Requirements

- Video camera, laptop/MacBook, gaming console or other video source with an available HDMI output
- Windows PC or MacBook with an available USB-A 3.2 port (or USB-A to USB-C adapter)

Package Includes

- U444-H4K6-CAP HDMI to USB Video Capture Adapter
- Quick Start Guide

Specifications

OVERVIEW



Powering Business Worldwide

TRIPP LITE
SERIES

UPC Code	037332287113
Device Compatibility	Chromebook; Computer; DVR; Laptop; Video Game System
Technology	HDMI; USB 3.x
Host Connector	USB 3.0 A (MALE)
VIDEO	
Video Input	USB A (MALE)
Video Output	HDMI (FEMALE)
Number of Monitors Supported	1
Video Ports	(1) HDMI (FEMALE)
Video Ports Details	HDCP 2.3
Resolutions Supported	USB Video Class (UVC) captures resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz MPJEG, or 4K @ 30 Hz raw data
Supported Resolutions	3840x4320 (4K); 1280x720 (720p); 1920x1080 (1080p)
Max Supported Video Resolution	3840 x 2160 @ 60 Hz
Extended Mode	No
Mirror Mode	No
Max Supported Color Depth	36-bit Deep Color
HDR Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:2:2; 4:4:4
EDID Support	Yes
DisplayPort Alt Mode	No
DSC Support	Yes
AUDIO	
Audio Specification	USB Audio Class (UAC) formats including 32KHz/44.1KHz/48KHz
INPUT	
Bus Powered	Yes
POWER	
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	(1) HDMI (FEMALE)



Powering Business Worldwide

TRIPP LITE
SERIES

Connector Plating	Nickel
PHYSICAL	
Color	Black
Material of Construction	PC+ABS PLASTIC
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Length (ft.)	0.98
Cable Length (m)	0.30
Cable Length (in.)	11.81
Cable Length (cm)	30
Unit Dimensions (hwd / in.)	0.630 x 1.850 x 3.940
Unit Packaging Type	Box
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 158°F (-20° to 70°C)
Operating Humidity Range	0% TO 40% RH (NON-CONDENSING)
Storage Humidity Range	20% TO 80% RH (NON-CONDENSING)
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.2 Gen 1 (up to 5 Gbps)
Data Transfer Rate	5 Gbps
Multi-Resolution Support	Yes
HDCP Specification	2.3
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); Trade Agreements Act (TAA); UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U444-H4K6-CAP](#)