

3-Port USB 3.x (5Gbps) Hub with LAN Port, USB-C to 3x USB-A Ports and Gigabit Ethernet, White

MODEL NUMBER: U460-003-3AG



Adds USB-A and Gigabit Ethernet ports to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

Description

The U460-003-3AG USB 3.1 Gen 1 USB-C Portable Hub/Adapter expands the potential of your tablet, laptop, MacBook, Chromebook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive and other USB peripherals, charging a mobile device, and connecting to a Gigabit Ethernet network—all at the same time.

The plug-and-play U460-003-3AG requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Three USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer, and each provides up to 0.9A for charging smartphones and other mobile devices. All ports support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

The RJ45 port offers access to a Gigabit Ethernet network when no Wi-Fi is available or when a wired connection offers faster speeds. Connect using a UTP cable (sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

Features

Turn Your Device's USB-C Port into a Multiport Workstation Ideal for adding USB peripherals, powering a mobile device and connecting to a Gigabit Ethernet network simultaneously Plug-and-play operation with no software, drivers or external power required White LED indicates unit is connected and receiving power About the size of a credit card for easy carrying in a pocket, purse or laptop bag

Connect USB Peripherals 3 USB-A ports accept flash drives, mice, keyboards, printers and other USB peripherals Each port provides up to 0.9A for charging mobile devices Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps Backward compatible with USB 2.0 and USB 1.1

Note: Host must support USB OTG (On-the-Go)

Access a Wired Gigabit Ethernet Network RJ45 port supports true 10/100/1000 Mbps network speeds Recommended for a faster wired network connection or getting online when no Wi-Fi is available

Built-In Cable with Reversible USB-C Connector Fumble-free reversible USB-C plug connects in either direction for quick connection every time

Highlights

- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- USB-A ports provide up to 0.9A each for charging devices
- Supports true 10/100/1000 Mbps Ethernet network speeds
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

System Requirements

- Source device with USB-C or Thunderbolt 3 port

Package Includes

- U460-003-3AG USB 3.1 Gen 1 USB-C Portable Hub/Adapter
- Owner's manual

Specifications



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

OVERVIEW	
UPC Code	037332193803
Product Type	Hub
Technology	Cat5/5e; Cat6; USB 3.x
Host Connector	USB C (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(3) USB A (FEMALE)
Data Ports Details	(3) USB-A - USB 3.2 Gen 1 (5 Gbps)
NETWORK	
Network Ports	RJ45 (FEMALE)
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	No
POWER	
Power Consumption (Watts)	2.50
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(3) USB 3.0 A (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Connector Plating	Nickel



Powering Business Worldwide



USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Power), Orange (Activity)
CHARGING	
Charging Ports / Amps	(3) 0.9A
PHYSICAL	
Color	White
Material of Construction	ABS, PVC
Cable Jacket Rating	VW-1
Shipping Dimensions (hwd / in.)	0.90 x 3.90 x 5.60
Shipping Weight (lbs.)	0.10
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Box
Unit Weight (lbs.)	0.09
Unit Weight (kg)	0.04
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	8.5 BTU/Hr
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output per USB port
COMMUNICATIONS	
Network Compatibility	1 Gbps (Gigabit)
IEEE Standards Supported	802.3; 802.3az; 802.3u; 802.3x
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	3
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
UASP Support	Yes
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes

Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U460-003-3AG](#)