

Cornell Dubilier

Cornell Dubilier Marketing, Inc
Liberty, South Carolina
TEL: 864-843-2277 FAX:864-843-3800

Engineering

Catalog Number: 101183U050BC2B

Customer Part Number: _____

Datasheet No.: 7178

Date: 09/16/03

Capacitance: 18000 μ F

Tolerance: - 10% + 75%

Working Volts: 50VDC

Surge Volts: 75VDC

Leakage Current @ 25°C: 1423 μ A

ESR @ 120Hz @ 25°C: 0.016 Ω max.

Ripple Current @ 120 Hz, 85°C: 16.7A

Diameter (D): 2.000 \pm 0.031 inches

Length (L): 4.125 \pm 0.062 inches


Total Length, W/Insulation (TL): 4.390 \pm 0.062 inches

Terminal Spacing (S): 0.875 \pm 0.016 inches

Terminal Thread (T): 10-32 UNF

Insulation: PVC

Operating Temperature: - 55°C ~ +105°C



“Controlled Copy” if viewed on CD Server or if copy is stamped in Red, Otherwise considered as an “Uncontrolled Copy”

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cornell Dubilier:](#)

[101183U050BC2B](#)