


# › Electromechanical Counters

## Impulse Counter

### CIM56x46

- › 6-digits Impulse counter
- › Capacity 999.999 impulses
- › Panel Mounted
- › Protection IP30
- › Excellent visibility due to the large digit size
- › Long service life



Screw

| Product selection |                          |               |                 |
|-------------------|--------------------------|---------------|-----------------|
| Type              | Operating frequency (Hz) | Rated Voltage | Part Number     |
| CIM56x46          | 50/60                    | 230 V~        | <b>99775609</b> |

| General characteristics                      |                             |
|--|-----------------------------|
| Counting capacity                            | 999.999                     |
| Height digits (mm)                           | 4                           |
| Reset to zero                                | Not included                |
| Max. count rate                              | 10 impulses/s               |
| Min. count rate (ms)                         | 50                          |
| Min pause time between 2 pulses (ms)         | 50                          |
| Max. pulse length (count coil)               | Unlimited                   |
| Voltage variation                            | ±10 %                       |
| Consumption                                  | 3 W                         |
| Mechanical life count function (operations)  | > 10 x 10 <sup>6</sup>      |
| Test voltage according to standard IEC 255-5 | 2 000 V                     |
| Protection Housing                           | IP30                        |
| Degree of terminal protection                | IP30                        |
| Environmental protection                     | Plated components           |
| Maintenance                                  | None                        |
| Operating position                           | Any                         |
| Temperature limits use (°C)                  | -5 → +50                    |
| Temperature limits stored (°C)               | -20 → +65                   |
| Humidity                                     | 45-85 % (non-condensing)    |
| Connections / Termination                    | With 2 - way terminal strip |
| Mounting                                     | Panel                       |
| Weight (g)                                   | 142                         |
| Certifications                               | CE, UKCA, RoHS compliant    |
| Approvals                                    | Parts used: UL              |

You have a project? Contact us on [www.crouzet.com](http://www.crouzet.com)

#### Description:


#### Crouzet Impulse Counters, accurate and durable solutions for pulse measurement needs

Crouzet's electromechanical impulse counters are reliable devices designed for measuring and recording electrical impulses in industrial applications. Crouzet's impulse counters use a combination of mechanical and electrical components to precisely count electrical pulses, offering a reliable solution for various industrial control and monitoring tasks.


For more information about: please visit [www.crouzet.com](http://www.crouzet.com)

Dimensions (mm)

Panel Mounted



Panel Cut-out



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Crouzet:](#)

[99775609](#)