

10G BASE-T TRANSFORMER MODULES

Industrial grade



- Compliant with IEEE 802.3 standards
- 120uH OCL Min with 9mA DC, at 100KHz 100mV
- PoE available, 300mA per channel
- Lead finish: Pure tin
- Moisture Sensitivity Level: 1


Electrical Specifications @ 25 °C – Operating Temperature – 40 °C to +85 °C

Part Number	Insertion Loss (dB MIN)		Return Loss (dB MIN)						Crosstalk (dB MIN)			DM to CM Rejection Ratio (dB MIN)			Dielectric Withstanding Voltage @60s (Vrms MIN)
	300 KHz	500 MHz	1 MHz	10 MHz	100 MHz	300 MHz	400 MHz	500 MHz	1 MHz	100 MHz	400 MHz	1 MHz	250 MHz	500 MHz	
R6001NL	-3.0	-1.8	-22	-24	-20	-12	-9	-8	-40	-37	-30	-40	-30	-22	1500

Notes: 1. Add suffix "T" to part number for Tape & Reel package (ie: **R6001NLT**).

Mechanical

R6001NL



Dimensions: inches[mm]
 Unless otherwise specified, all tolerances are ± .010 [0.25]
 Weight.....2.0grams MAX
 Tape and Reel.....300pcs/reel
 Tube.....25pcs/tube




10GBASE-T TRANSFORMER MODULES

Industrial grade




Electrical Schematic

R6001NL



Non-Lead Recommended Reflow Profile (Based on J-STD-020D)



T_{SMIN} (°C)	T_{SMAX} (°C)	T_L (°C)	T_P (°C MAX)	t_s (s)	t_L (s)	t_p (s MAX)	Ramp-up rate (T_L to T_P)	Ramp-down rate (T_P to T_L)	Time 25°C to peak temperature (s MAX)
150	200	217	245	60-120	60-150	30	3°C/s MAX	6°C/s MAX	480

Notes:

1. All temperatures measured on the package leads.
2. Maximum times of reflow cycle: 2.

For More Information

iNRCORE,LLC
311 Sinclair Road Bristol,
PA 19007-6812 U.S.A
Tel: + 1.215.781.6400
Fax: +1.215.7816430

Dongguan iNRCORE Co. Ltd
No.7, An Li Road, Changan Town,
Dongguan City, China
Tel: +0769 8165 9962

Global Sales Representatives and Locations:
<http://www.inrcore.com>

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2020. iNRCORE, LLC. All rights reserved.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[iNRCORE:](#)

[R6001NL](#) [R6001NLT](#)