

G80B0C-P03LJG0-0000
series_b, type_g8



General information

Part number	G80B0C-P03LJG0-0000
Termination	solder
Size	0
Locking principle	break , push
Keying	0_key



CODING: 0*

POSITIONS: 3 Positions

PANEL CUT OUT:

DIMENSIONS:

Contact insert description

Number of contacts	3
Contact type	sockets
Contact diameter	09mm
Insulator material	peek
Wire cross section	22_awg
Termination	solder
Termination diameter	085mm

reverse_gender_on_request

Technical information

Max. creepage and air clearance distance	08_mm	10_mm
Nominal current single contact	075_a	iec_60512_5_2
Nominal current insert	7,5 A	vde_0298_4
Test voltage	12_kv_ac	sae_13441

safety_text

Mechanical and environmental data

Degree of protection*	ip68
Operating temperature	40_120_c
Mating cycles	5000

mated_unmated

Material and surface treatments

Housing	m_chrome
Contact	cu_alloy_gold

safety_text_2
 ul_text
 illustrative_text

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ODU:

[G80B0C-P03LJG0-0000](#)