




UNCONTROLLED DOCUMENT



NOTES:
 HOLE SIZE .275 / .290
 PANEL THICKNESS RANGE .031 / .156
 SCREW SIZE #8-#10

TOLERANCES UNLESS NOTED

- $\pm .005$ ON DIMENSIONS THRU .625
- $\pm .008$ ON DIMENSIONS .626 THRU 1.000
- $\pm .010$ ON DIMENSIONS 1.001 THRU 1.500
- $\pm .015$ ON DIMENSIONS LARGER THAN 1.500
- $\pm .015$ ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT
 TO DISCONTINUE ITEMS,
 CHANGE SPECIFICATIONS
 OR DESIGN AT ANY TIME
 WITHOUT NOTICE AND
 WITHOUT INCURRING
 ANY OBLIGATIONS

PROPERTY OF
MICRO PLASTICS INC.

CATALOG DRAWING
 ROUND HEAD GROMMET NUTS
 MICRO P/N 60SGN00100
 DWG. # 60SGN00100
 FILE SERVER\ENG\WEB

MATERIAL: NYLON 6/6

DATE

SCALE
 4:1

DB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[60SGN00100](#)