


**UNCONTROLLED DOCUMENT**

NOTES:

PARTS ARE PACKAGED 100 PIECES PER BAG.  
DRILLED HOLE DIAMETER [4.80 MM] .189  
MAX. PANEL THICKNESS [3.20 MM] .125  
MAX. STRENGTH [18 KG] 40 LBS.



TOLERANCES UNLESS NOTED

- ±.005 ON DIMENSIONS THRU .625
- ±.008 ON DIMENSIONS .626 THRU 1.000
- ±.010 ON DIMENSIONS 1.001 THRU 1.500
- ±.015 ON DIMENSIONS LARGER THAN 1.500
- ±.015 ON FRACTIONAL DIMENSIONS

**WE RESERVE THE RIGHT  
TO DISCONTINUE ITEMS,  
CHANGE SPECIFICATIONS  
OR DESIGN AT ANY TIME  
WITHOUT NOTICE AND  
WITHOUT INCURRING  
ANY OBLIGATIONS**

PROPERTY OF  
**MICRO PLASTICS INC.**

CATALOG DRAWING  
PUSH MOUNT CABLE TIE  
MICRO P/N NTA15535PMTG  
DWG. # NTA15535PMTG  
FILE SERVER\ENG\WEB

MATERIAL: 6/6 NYLON

DATE

SCALE  
1:1

**DSB**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[NTA15535PMTG](#)