


REV.	DATE	DESCRIPTION
NC	06/21/05	INITIAL RELEASE



NOTE:  
 1. CRIMPED FERRULE  
 HEX CRIMP SIZE .255"  
 2. CONTACT PIN TO SOLDER

NO.	DESCRIPTION	MATERIAL	FINISH	QTY	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:	APPROVALS	DATE	PART DESCRIPTION			
8										<b>Amphenol Connex</b> TNC REVERSE POLARITY R/A CRIMP PLUG (FOR BELDEN RG-8/X, TIMES LMR-240)			
7								DRAWN	G.R.S.		06/21/05		
6	COVER	BRASS	NICKEL	1		0.5 - 8mm ± 0.20mm	.020 - .315 = ± 0.007"	CHECKED					
5	FERRULE	COPPER	NICKEL	1		8 - 30mm ± 0.40mm	.315 - 1.180 = ± 0.015"	ISSUED					
4	CONTACT PIN	PHOS. BRONZE	GOLD	1		30 - 120mm ± 0.50mm	1.180 - 4.724 = ± 0.020"	SHEET	1 OF 1				
3	INSULATOR	TEFLON	NATURAL	1									
2	BODY/SHELL	BRASS	NICKEL	1							PART NO. 1222414RP		
1	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING			CAD FILE	C:/122/122414RP.DWG		DWG. NO. 122414RP.DWG	REV. NC	SIZE A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122414RP](#)