



## T2212 THERMAL TRANSFER PRINTER

The T2212 is a robust entry level industrial computer-driven 300dpi thermal transfer printer. Specially designed to print on a wide range of TE Connectivity (TE) labels, cable markers and identification heat shrink sleeves. New full-color touch screen interface, with intuitive icon-based setting adjustments. Various preloaded tutorials answer commonly-asked questions without the unit having to connect to the internet. The Printer is equipped with Additional RS232 port and Flash card, USB, Ethernet and serial ports. Product and ribbon can be loaded quickly and easily, designed for a quick setup and when changing between products. For optimal print results we recommend using the T2212 Printer in conjunction with TE identification product, ribbon and WINTOTAL software.

T2212 Printer can also be purchased together with WINTOTAL Software, one part number (1-2186528-1) is ideal for new and existing customers setting up a new printing location.

# T2212 Thermal Transfer Printer

## BENEFITS

- Print on a large range of materials, including heat-shrink sleeves, continuous tube, cable tags, panel label, high temperature electronic and industrial labels.
- Quick and easy to change product and ribbon.
- Printer settings can be adjusted quickly and easily with an intuitive color touch screen.

## APPLICATIONS

- Office environment.
- Industrial environment.

## FEATURES

- Entry level printer for low / medium volume printing of TE Identifications products.
- Side loading of labels and ribbons results in a shorter setup time and increased productivity.
- Intuitive, icon-based printer setting adjustments and integrated help videos.

## ELECTRICAL

- 100 to 240VAC - 50/60Hz, PFC.

## MATERIALS

- Plastic and Metal.

Part Number	Description
-------------	-------------

1-2186527-1	T2212-PRINTER
1-2186528-1	T2212-SWARE-PRINTER
1-2186529-1	T2212-CUTTER
1-2186530-1	T2212-PERFORATOR
EC9926-000	PRINTER-UNIVERSAL-REEL-HOLDER

## te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

© 2020 TE Connectivity. All Rights Reserved.

2-1773983-2 02/20 AK