



# DEUTSCH QPL CONTACTS QUICK REFERENCE GUIDE

---

The Performance Leader for Mil-Spec Contacts

## High Performance

- Achieve enhanced durability — 1500 cycles (insertion/withdrawals)
- Terminate to aluminum or standard wires

## More Compatibility

- Use with full range of mil-spec connectors
- Meet ASE/EN requirements

| Contact Part No.                                                                                                                  |                | Contact Size | Insertion / Removal Tool    |                             | Crimping            |                     |
|-----------------------------------------------------------------------------------------------------------------------------------|----------------|--------------|-----------------------------|-----------------------------|---------------------|---------------------|
|                                                                                                                                   |                |              | Insertion                   | Withdraw                    | Crimp Tool          | Positioner          |
| Military                                                                                                                          | TE             | AWG          | M81969 Slash No.            | M81969 Slash No. (Wired)    | M22520 Slash No.    | M22520 Slash No.    |
| <b>M39029 Contacts</b>                                                                                                            |                |              |                             |                             |                     |                     |
| <b>M39029/1 Pin Contacts (For AS81714 Series I Terminal System)</b>                                                               |                |              |                             |                             |                     |                     |
| /1-100                                                                                                                            | 2560-214-1631  | 16/22        | /14-10                      | /14-10                      | /2-01               | /2-11               |
| /1-101                                                                                                                            | 2560-215-1631L | 16/20        | /14-10                      | /14-10                      | /1-01, /2-01        | /1-02, /2-11        |
| /1-102                                                                                                                            | 2560-216-1431  | 14/16        | /14-03                      | /14-03                      | /1-01               | /1-02               |
| /1-103                                                                                                                            | 2560-217-1231  | 12           | /14-04                      | /14-04                      | /1-01               | /1-02               |
| /1-507                                                                                                                            | 2560-218-2031  | 20/22D       | /14-01, /1-04, /8-01, /8-02 | /14-01, /1-04, /8-01, /8-02 | /1-01               | /2-32               |
| <b>M39029/4 Pin Contacts (For MIL-DTL-26482 Series II, -83723 Series III, -83733, and AS81703 Connectors)</b>                     |                |              |                             |                             |                     |                     |
| /4-110                                                                                                                            | 0641-1-2031L   | 20           | /14-11, /8-205              | /14-11, /8-206              | /1-01, /2-01, /7-01 | /1-02, /2-02, /7-02 |
| /4-111                                                                                                                            | 0641-2-1631L   | 16           | /14-03, /8-207              | /14-03, /8-208              | /1-01, /7-01        | /1-02, /7-03        |
| /4-112                                                                                                                            | 109026-31      | 16/20        | /14-03, /8-207              | /14-03, /8-208              | /1-01, /7-01        | /1-02, /7-03        |
| /4-113                                                                                                                            | 0641-3-1231L   | 12           | /14-04, /8-209              | /14-04, /8-210              | /1-01               | /1-02               |
| /4-114                                                                                                                            | 109028-31L     | 12/16        | /14-04, /8-209              | /14-04, /8-210              | /1-01               | /1-02               |
| <b>M39029/5 Socket Contacts (For MIL-DTL-26482 Series II, -83723 Series III, -83733, and AS81703 Connectors)</b>                  |                |              |                             |                             |                     |                     |
| /5-115                                                                                                                            | 100503L        | 20           | /14-11, /8-05               | /14-11, /8-06               | /1-01, /2-01, /7-01 | /1-02, /2-02, /7-02 |
| /5-116                                                                                                                            | 100504L        | 16           | /14-03, M91659/8-07         | /14-03, /8-08               | /1-01, /7-01        | /1-02, /7-03        |
| /5-117                                                                                                                            | 109027         | 16/20        | /14-03, /8-207              | /14-03, /8-208              | /1-01, /7-01        | /1-02, /7-03        |
| /5-118                                                                                                                            | 100505L        | 12           | /14-04, /8-09               | /14-04, /8-210              | /1-01               | /1-02               |
| /5-119                                                                                                                            | 109029         | 12/16        | /14-04, /8-209              | /14-04, /8-210              | /1-01               | /1-02               |
| <b>M39029/10 Socket Contacts — Thermocouples (For MIL-DTL-26482 Series II, -83723 Series III, -83733, and AS81703 Connectors)</b> |                |              |                             |                             |                     |                     |
| /10-521                                                                                                                           | 7362-255-1601  | 16           | /14-03                      | /14-03                      | /1-01, /7-01        | /1-02, /7-03        |
| /10-522                                                                                                                           | 7362-226-1601  | 16           | /14-03                      | /14-03                      | /1-01, /7-01        | /1-02, /7-03        |
| <b>M39029/11 Pin Contacts (For AS81659 Series II Connectors)</b>                                                                  |                |              |                             |                             |                     |                     |
| /11-144                                                                                                                           | 2560-212-2231  | 22           | /1-01                       | /1-01                       | /2-01               | /2-23               |
| /11-145                                                                                                                           | 2560-212-2031  | 20           | /1-02                       | /1-02                       | /2-01, /7-01        | /2-08, /7-02        |
| <b>M39029/12 Socket Contacts (For AS81659 Series II Connectors)</b>                                                               |                |              |                             |                             |                     |                     |
| /12-148                                                                                                                           | 2562-209-2231  | 22           | /1-01                       | /1-01                       | /2-01               | /2-23               |
| /12-149                                                                                                                           | 2562-209-2031  | 20           | /1-02                       | /1-02                       | /2-01, /7-01        | /2-08, /7-02        |
| <b>M39029/16 Socket Contacts (For AS81511 Series IV Connectors)</b>                                                               |                |              |                             |                             |                     |                     |
| /16-166                                                                                                                           | 81542-238L     | 23/28        | /16-04                      | /16-04                      | /2-01               | /2-13               |
| /16-167                                                                                                                           | 81542-23L      | 23/22        | /16-04                      | /16-04                      | /2-01               | /2-13               |
| /16-168                                                                                                                           | 81542-20L      | 20           | /16-01                      | /16-01                      | /2-01               | /2-14               |
| /16-169                                                                                                                           | 81542-16L      | 16           | /16-02                      | /16-02                      | /2-01               | /2-15               |
| /16-170                                                                                                                           | 81542-12L      | 12           | /16-03                      | /16-03                      | /1-01               | /1-09               |
| <b>M39029/17 Socket Contacts (For AS81511 Series III Connectors)</b>                                                              |                |              |                             |                             |                     |                     |
| /17-171                                                                                                                           | 81543-238L     | 23/28        | /16-04                      | /16-04                      | /2-01               | /2-16               |
| /17-172                                                                                                                           | 81543-23L      | 23/22        | /16-04                      | /16-04                      | /2-01               | /2-16               |
| /17-173                                                                                                                           | 81543-20L      | 20           | /16-01                      | /16-01                      | /2-01               | /2-17               |
| /17-174                                                                                                                           | 81543-16L      | 16           | /16-02                      | /16-02                      | /2-01               | /2-18               |
| /17-175                                                                                                                           | 81543-12L      | 12           | /16-03                      | /16-03                      | /1-01               | /1-10               |

Part numbers ending in trailing L are available with localized gold plating, according to ASTM B 488, Type II, Code C: 50 micro-inches over nickel underplating. For full plating, remove the trailing L.  
Italicized part numbers are for the TE's Evreux facility. All others are for TE's Oceanside facility.  
For wire size, a double number indicates Mating End/Crimp End.

| Contact Part No.                                                                                                  |                        | Contact Size | Insertion / Removal Tool |                          | Crimping            |                     |
|-------------------------------------------------------------------------------------------------------------------|------------------------|--------------|--------------------------|--------------------------|---------------------|---------------------|
|                                                                                                                   |                        |              | Insertion                | Withdraw                 | Crimp Tool          | Positioner          |
| Military                                                                                                          | TE                     | AWG          | M81969 Slash No.         | M81969 Slash No. (Wired) | M22520 Slash No.    | M22520 Slash No.    |
| <b>M39029 Contacts</b>                                                                                            |                        |              |                          |                          |                     |                     |
| <b>M39029/18 Pin Contacts (For AS81511 Series III and IV Connectors)</b>                                          |                        |              |                          |                          |                     |                     |
| /18-176                                                                                                           | 81541-238L             | 23/28        | /16-04                   | /16-04                   | /2-01               | /2-13               |
| /18-177                                                                                                           | 81541-23L              | 23/22        | /16-04                   | /16-04                   | /2-01               | /2-13               |
| /18-178                                                                                                           | 81541-20L              | 20           | /16-01                   | /16-01                   | /2-01, /7-01        | /2-14, /7-02        |
| /18-179                                                                                                           | 81541-16L              | 16           | /16-02                   | /16-02                   | /2-01, /7-01        | /2-15, /7-03        |
| /18-180                                                                                                           | 81541-12L              | 12           | /16-03                   | /16-03                   | /1-01               | /1-09               |
| <b>M39029/22 Socket Contacts (For AS81714 Series II Terminal System and AS81511 Series III and IV Connectors)</b> |                        |              |                          |                          |                     |                     |
| /22-191                                                                                                           | CTS-S22/22             | 22           |                          | —                        | /7-01               | /7-11               |
| /22-192                                                                                                           | CTS-S20/20             | 20           | /14-10                   | —                        | /7-01               | /7-12               |
| /22-193                                                                                                           | CTS-S16/16             | 16           | /14-03                   | —                        | /7-01               | /7-13               |
| /22-605                                                                                                           | CTS-S12/12             | 12           | /8-10, /16-03            | —                        | /1-01               | /2-34, /31-02       |
| <b>M39029/28 Pin Contacts • Coax (For MIL-DTL-38999 Series I, II, III, and IV Connectors)</b>                     |                        |              |                          |                          |                     |                     |
| /28-211                                                                                                           | 6162-233-1277          | 12           | /8-09, /14-04            | /8-10, /14-04            | /2-01, /31-01       | /2-34, /31-02       |
| /28-409                                                                                                           | 6162-234-1277          | 12           | /8-09, /14-04            | /8-10, /14-04            | /2-01, /31-01       | /2-34, /31-02       |
| /28-414                                                                                                           | 6162-239-1277          | 12           | /8-09, /14-04            | /8-10, /14-04            | /2-01, /31-01       | /2-34, /31-02       |
| <b>M39029/29 Pin Contacts (For AS50151, MS5450, and MIL-DTL-83723 Series II Connectors)</b>                       |                        |              |                          |                          |                     |                     |
| /29-212                                                                                                           | 0660-206-1631L         | 16           | /14-03                   | /14-03                   | /1-01, /7-01        | /1-02, /7-03        |
| /29-213                                                                                                           | 0660-206-1282          | 12           | /14-04                   | /14-04                   | M22750/1-01         | /1-02               |
| /29-214                                                                                                           | 0660-206-0882 (Silver) | 8            | —                        | /29-02                   | /23-01              | —                   |
| /29-215                                                                                                           | 0660-206-0482 (Silver) | 4            | —                        | /29-03                   | /23-01              | —                   |
| /29-216                                                                                                           | 0660-206-0082 (Silver) | 0            | —                        | /29-04                   | /23-01              | —                   |
| <b>M39029/30 Socket Contacts (For AS50151, MS5450, and MIL-DTL-83723 Series II Connectors)</b>                    |                        |              |                          |                          |                     |                     |
| /30-217                                                                                                           | 0662-212-1631L         | 16S/16       | /14-03                   | /14-03                   | /1-01, /7-01        | /1-02, /7-03        |
| /30-218                                                                                                           | 0662-207-1631L         | 16           | /14-03                   | /14-03                   | /1-01, /7-01        | /1-02, /7-03        |
| /30-219                                                                                                           | 0662-207-1282 (Silver) | 12           | /14-04                   | /14-04                   | /1-01               | /1-02               |
| /30-220                                                                                                           | 0662-207-0882 (Silver) | 8            | —                        | /29-02                   | /23-01              | —                   |
| /30-221                                                                                                           | 0662-207-0482 (Silver) | 4            | —                        | /29-03                   | /23-01              | —                   |
| /30-222                                                                                                           | 0662-207-0082 (Silver) | 0            | —                        | /29-04                   | /23-01              | —                   |
| <b>M39029/31 Pin Contacts (For MIL-DTL-26482 Series I and -26500 Connectors)</b>                                  |                        |              |                          |                          |                     |                     |
| /31-228                                                                                                           | 4160-203-1631L         | 16           | /14-03, /17-04           | /19-01                   | /1-01, /7-01        | /1-02BLUE, /7-03    |
| /31-229                                                                                                           | 4160-204-1631L         | 16           | /14-03, /17-04           | /19-01                   | /1-01, /7-01        | /1-02BLUE, /7-03    |
| /31-240                                                                                                           | 0004-058-100L          | 20           | /14-10, /17-03           | /19-06                   | /1-01, /2-01, /7-01 | /1-02, /2-02, /7-02 |
| /31-627                                                                                                           | 4160-202-2031L         | 20           | /14-10, /17-03           | /19-06                   | /1-01, /2-01, /7-01 | /1-02, /2-02, /7-02 |
| <b>M39029/32 Socket Contacts (For MIL-DTL-26482 Series I and -26500 Connectors)</b>                               |                        |              |                          |                          |                     |                     |
| /32-247                                                                                                           | 4162-201-1631L         | 16           | /14-03, /17-04           | /19-01                   | /1-01, /7-01        | /1-02, /7-03        |
| /32-248                                                                                                           | 4162-202-1631L         | 16           | /14-03, /17-04           | /19-01                   | /1-01, /7-01        | /1-02, /7-03        |
| /32-259                                                                                                           | 0007-008-100L          | 20           | /14-10, /17-03           | /19-06                   | /1-01, /2-01, /7-01 | /1-02, /2-02, /7-02 |
| /32-260                                                                                                           | 4109-207-2000L         | 20           | /14-10, /17-03           | /19-06                   | /1-01, /2-01, /7-01 | /1-02, /2-02, /7-02 |

Part numbers ending in trailing L are available with localized gold plating, according to ASTM B 488, Type II, Code C: 50 micro-inches over nickel underplating. For full plating, remove the trailing L.  
Italicized part numbers are for the TE's Evreux facility. All others are for TE's Oceanside facility.  
For wire size, a double number indicates Mating End/Crimp End.

| Contact Part No.                                                                                         |                       | Contact Size | Insertion / Removal Tool |                          | Crimping         |                  |
|----------------------------------------------------------------------------------------------------------|-----------------------|--------------|--------------------------|--------------------------|------------------|------------------|
|                                                                                                          |                       |              | Insertion                | Withdraw                 | Crimp Tool       | Positioner       |
| Military                                                                                                 | TE                    | AWG          | M81969 Slash No.         | M81969 Slash No. (Wired) | M22520 Slash No. | M22520 Slash No. |
| <b>M39029 Contacts</b>                                                                                   |                       |              |                          |                          |                  |                  |
| <b>M39029/63 Socket Contacts (For MIL-DTL-24308 Connectors)</b>                                          |                       |              |                          |                          |                  |                  |
| /63-368                                                                                                  | 2562-201-2031L        | 20           | /39-01, /1-02            | /39-01, /1-02            | /2-01            | /2-08            |
| <b>M39029/64 Pin Contacts (For MIL-DTL-24308 Connectors)</b>                                             |                       |              |                          |                          |                  |                  |
| /64-369                                                                                                  | 2560-201-2031L        | 20           | /39-01, /1-02            | /39-01, /1-02            | /2-01            | /2-08            |
| <b>M39029/75 Socket Contacts • Coax (For MIL-DTL-38999 Series I, III, and IV Connectors)</b>             |                       |              |                          |                          |                  |                  |
| /75-416                                                                                                  | 6162-217-1277 (Au/Ni) | 12           | /8-09, /14-04            | /8-10, /14-04            | /2-01, /31-01    | /2-34, /31-02    |
| /75-417                                                                                                  | 6162-218-1277 (Au/Ni) | 12           | /8-09, /14-04            | /8-10, /14-04            | /2-01, /31-01    | /2-34, /31-02    |
| /75-418                                                                                                  | 6162-219-1277 (Au/Ni) | 12           | /8-09, /14-04            | /8-10, /14-04            | /2-01, /31-01    | /2-34, /31-02    |
| /75-419                                                                                                  | 6162-220-1277 (Au/Ni) | 12           | /8-09, /14-04            | /8-10, /14-04            | /2-01, /31-01    | /2-34, /31-02    |
| /75-421                                                                                                  | 6162-222-1277 (Au/Ni) | 12           | /8-09, /14-04            | /8-10, /14-04            | /2-01, /31-01    | /2-34, /31-02    |
| /75-422                                                                                                  | 6162-223-1277 (Au/Ni) | 12           | /8-09, /14-04            | /8-10, /14-04            | /2-01, /31-01    | /2-34, /31-02    |
| /75-423                                                                                                  | 6162-224-1277 (Au/Ni) | 12           | /8-09, /14-04            | /8-10, /14-04            | /2-01, /31-01    | /2-34, /31-02    |
| <b>M39029/76 Pin Contacts • Coax (For MIL-DTL-38999 Series I, II, III, and IV and -24308 Connectors)</b> |                       |              |                          |                          |                  |                  |
| /76-424                                                                                                  | 6162-229-1677 (Au/Ni) | 16           | /8-07, /14-03            | /8-08, /14-03            | /2-01, /4-01     | /2-35, /4-02     |
| /76-425                                                                                                  | 6162-230-1677 (Au/Ni) | 16           | /8-07, /14-03            | /8-08, /14-03            | /2-01, /4-01     | /2-35, /4-02     |
| /76-426                                                                                                  | 6162-231-1677 (Au/Ni) | 16           | /8-07, /14-03            | /8-08, /14-03            | /2-01, /4-01     | /2-35, /4-02     |
| /76-427                                                                                                  | 6162-232-1677 (Au/Ni) | 16           | /8-07, /14-03            | /8-08, /14-03            | /2-01, /4-01     | /2-35, /4-02     |
| <b>M39029/77 Socket Contacts • Coax (For MIL-DTL-38999 Series I, III, and IV Connectors)</b>             |                       |              |                          |                          |                  |                  |
| /77-428                                                                                                  | 6162-213-1677 (Au/Ni) | 16           | /8-07, /14-03            | /8-08, 14-03             | /2-01, /4-01     | /2-35, /4-02     |
| /77-429                                                                                                  | 6162-214-1677 (Au/Ni) | 16           | /8-07, /14-03            | /8-08, 14-03             | /2-01, /4-01     | /2-35, /4-02     |
| /77-430                                                                                                  | 6162-215-1677 (Au/Ni) | 16           | /8-07, /14-03            | /8-08, 14-03             | /2-01, /4-01     | /2-35, /4-02     |
| /77-431                                                                                                  | 6162-216-1677 (Au/Ni) | 16           | /8-07, /14-03            | /8-08, 14-03             | /2-01, /4-01     | /2-35, /4-02     |
| <b>M39029/78 Socket Contacts • Coax (For MIL-DTL-38999 Series II and -24308 Connectors)</b>              |                       |              |                          |                          |                  |                  |
| /78-432                                                                                                  | 6162-253-1677 (Au/Ni) | 16           | /8-07, /14-03            | /8-08, 14-03             | /2-01, /4-01     | /2-35, /4-02     |
| /78-433                                                                                                  | 6162-254-1677 (Au/Ni) | 16           | /8-07, /14-03            | /8-08, 14-03             | /2-01, /4-01     | /2-35, /4-02     |
| /78-434                                                                                                  | 6162-255-1677 (Au/Ni) | 16           | /8-07, /14-03            | /8-08, 14-03             | /2-01, /4-01     | /2-35, /4-02     |
| /78-435                                                                                                  | 6162-256-1677         | 16           | /8-07, /14-03            | /8-08, 14-03             | /2-01, /4-01     | /2-35, /4-02     |

Part numbers ending in trailing L are available with localized gold plating, according to ASTM B 488, Type II, Code C: 50 micro-inches over nickel underplating. For full plating, remove the trailing L.  
Italicized part numbers are for the TE's Evreux facility. All others are for TE's Oceanside facility.  
For wire size, a double number indicates Mating End/Crimp End.

| Contact Part No.                                                                                                 |                | Contact Size | Insertion / Removal Tool |                          | Crimping            |                     |
|------------------------------------------------------------------------------------------------------------------|----------------|--------------|--------------------------|--------------------------|---------------------|---------------------|
|                                                                                                                  |                |              | Insertion                | Withdraw                 | Crimp Tool          | Positioner          |
| Military                                                                                                         | TE             | AWG          | M81969 Slash No.         | M81969 Slash No. (Wired) | M22520 Slash No.    | M22520 Slash No.    |
| <b>M39029 Contacts</b>                                                                                           |                |              |                          |                          |                     |                     |
| <b>M39029/83 Pin Contacts (For MIL-DTL-28840 Connectors)</b>                                                     |                |              |                          |                          |                     |                     |
| /83-450                                                                                                          | 2560-221-2031L | 20/22        | /33-01                   | /34-01                   | /34-01              | /34-02              |
| /83-451                                                                                                          | 2560-222-2031L | 20/28        | /33-01                   | /34-01                   | /34-01              | /34-02              |
| /83-508                                                                                                          | 2560-220-2031L | 20           | /33-01                   | /34-01                   | /34-01              | /34-02              |
| <b>M39029/84 Socket Contacts (For MIL-DTL-28840 Connectors)</b>                                                  |                |              |                          |                          |                     |                     |
| /84-452                                                                                                          | 2562-214-2031L | 20/22        | /33-01                   | /34-01                   | /34-01              | /34-02              |
| /84-453                                                                                                          | 2562-215-2031L | 20/28        | /33-01                   | /34-01                   | /34-01              | /34-02              |
| /84-509                                                                                                          | 2562-213-2031L | 20           | /33-01                   | /34-01                   | /34-01              | /34-02              |
| <b>M39029/90 Pin Contacts • Twinax (For MIL-DTL-38999 Series III and IV Connectors)</b>                          |                |              |                          |                          |                     |                     |
| /90-529                                                                                                          | 6162-283-0877  | 8            | /14-12                   | /14-12                   | /2-01, /5-01        | /2-37, /5-105       |
| <b>M39029/91 Socket Contacts • Twinax (For MIL-DTL-38999 Series III and IV Connectors)</b>                       |                |              |                          |                          |                     |                     |
| /91-530                                                                                                          | 6162-284-0877  | 8            | /14-12                   | /14-12                   | /2-01, /5-01        | /2-37, /5-105       |
| <b>M39029/101 Socket Contacts (For MIL-DTL-12883 Sockets and MIL-PRF-Relays)</b>                                 |                |              |                          |                          |                     |                     |
| /101-553                                                                                                         | 1662-213-2031L | 20           | /16-01                   | /16-01                   | /7-01, /1-01        | /7-12               |
| /101-554                                                                                                         | 1662-213-1631L | 16           | /16-02                   | /16-02                   | /7-01               | /7-13               |
| <b>M39029/102 Pin Contacts • Coax (For MIL-DTL-38999 Series III and IV Connectors)</b>                           |                |              |                          |                          |                     |                     |
| /102-558                                                                                                         | 6162-324-1231  | 12           | /8-09, /14-04            | /8-10, /14-04            | /5-01               | —                   |
| <b>M39029/103 Socket Contacts • Coax (For MIL-DTL-38999 Series III and IV Connectors)</b>                        |                |              |                          |                          |                     |                     |
| /103-559                                                                                                         | 6162-325-1231  | 12           | /8-09, /14-04            | /8-10, /14-04            | /5-01               | —                   |
| <b>M39029/106 Socket Contacts (For MIL-DTL-38999 Series III and IV, AS29600 Series A, and EN3645 Connectors)</b> |                |              |                          |                          |                     |                     |
| /106-614                                                                                                         | 12333-22       | 22/22D       | /14-01, /8-01            | /14-01, /8-02            | /2-01, /7-01        | /2-07, /7-05        |
| /106-615                                                                                                         | 12333-20       | 20           | /14-10, /8-05            | /14-10, /8-06            | /1-01, /2-01, /7-01 | /1-04, /2-10, /7-08 |
| /106-616                                                                                                         | 12333-16       | 16           | /14-03, /8-07            | /14-03, /8-08            | /1-01, /7-01        | /1-04, /7-04        |
| /106-617                                                                                                         | 12333-12       | 12           | /14-04, /8-09            | /14-04, /8-10            | /1-01               | /1-04               |
| <b>M39029/107 Pin Contacts (For MIL-DTL-38999 Series III and IV, AS29600 Series A, and EN3645 Connectors)</b>    |                |              |                          |                          |                     |                     |
| /107-620                                                                                                         | 12331-22       | 22/22D       | /14-01, /8-01            | /14-01, /8-02            | /2-01, /7-01        | /2-07, /7-05        |
| /107-621                                                                                                         | 12331-20       | 20           | /14-10, /8-05            | /14-10, 8-06             | /1-01, /2-01, /7-01 | /1-04, /2-10, /7-08 |
| /107-622                                                                                                         | 12331-16       | 16           | /14-03, /8-07            | /14-10, 8-06             | /1-01, /7-01        | /1-04, /7-04        |
| /107-623                                                                                                         | 12331-12       | 12           | /14-04, /8-09            | /14-04, /8-10            | /1-01               | /1-04               |

Part numbers ending in trailing L are available with localized gold plating, according to ASTM B 488, Type II, Code C: 50 micro-inches over nickel underplating. For full plating, remove the trailing L.  
Italicized part numbers are for the TE's Evreux facility. All others are for TE's Oceanside facility.  
For wire size, a double number indicates Mating End/Crimp End.

---

## Connect With Us

We make it easy to connect with our experts and are ready to provide all the support you need.

Visit [te.com/support](https://te.com/support) to chat with a Product Information Specialist.

---

### te.com

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2024 TE Connectivity. All Rights Reserved.

1-1773735-3 06/24

### DEUTSCH CONTACTS QRG

TE Connectivity  
Aerospace, Defense & Marine  
2900 Fulling Mill Road  
Middletown, PA 17057

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[38946-22L](#)