


## HEYClip™ Locking Releasable Wire Clips - Adhesive-Back Mount


MAXIMUM BUNDLE DIAMETER	RATED STATIC LOAD	PART NO. Adhesive	NEW!			DESCRIPTION	FOOTPRINT		OVERALL HEIGHT		CLAMP WIDTH	
			Standard	NEW! Black	NEW! Super Black		A x B	C	D			
in. mm.	lb.	Gray	Black	Black		in.	mm.	in.	mm.	in.	mm.	
<b>WCA Series</b>												
.19	4,7	1/2	3857	3917	-	WCA 187-500	.74 x .62	18,8 x 15,7	.34	8,6	.39	9,9
.25	6,4	3/4	3858	3918	3918A	WCA 250-750	1.00 x .87	25,4 x 22,1	.42	10,7		
.38	9,5	1	3859	3919	3919A	WCA 375-1000	1.00 x 1.00	25,4 x 25,4	.50	12,7	.63	16,0
.50	12,7	1-1/4	3860	3920	3920A	WCA 500-1250	1.00 x 1.21	25,4 x 30,7	.68	17,3		
.75	19,1	1-3/4	3861	3921	-	WCA 750-1750	1.15 x 1.45	29,2 x 36,8	.99	25,1	.64	16,3
1.00	25,4	4	3867	3923	-	WCA1000-4000	1.98 x 2.24	50,3 x 56,9	1.37	34,8	1.26	32,0
1.50	38,1	6	3868	3930	-	WCA 1500-6000	2.42 x 2.95	61,5 x 74,9	1.77	45,0	1.31	33,3

Standard color gray or black. Super duty adhesive backing available as shown.


- Adhesive backing on part has a tab for easy removal.
- Releasable and reusable clips for easy wire bundle routing.
- Quick and easy installation—simply peel off backing and press into place.
- Multiple sizes for bundles from .19" (4,7 mm) to 1.50" (38,1 mm) in diameter.
- Static Loads pertain to parts fastened to a flat, clean, and dry surface.
- Three sizes in Super Adhesive Black.
- Super adhesive temperature range is -40°F (-40°C) to 250°F (121°C).
- Recommended storage temperature from 60°F (16°C) to 80°F (27°C) with approximate relative Storage Temperature humidity of 50%




### Adhesive-Back Mount Instructions



HEYClip attaches easily to any commercial surface. Tab on backing strips ensures easy removal.



Unique closure operates easily, locks securely. When closed, HEYClip will not release until push tab is released.



HEYClip opens easily to permit removal of bundle.

Material	Nylon 6/6
Flammability Rating	94V-2
Temperature Range	-20°F (-29°C) to 150°F (66°C)

Quick Specs

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3860C](#)