

DETAILS


Product Number	CA11892_STRADA-SQ-T-DW
Family	Strada
Type	Assembly
Color	clear
Diameter	25 + 25 mm
Height	12,65 mm
Style	square
Optic Material	PMMA
Holder Material	
Fastening	pin, tape, screw
Status	production ready
ROHS Compliant	Yes
Date Updated	26/08/2014




OPTICAL PROPERTIES

LED	Viewing Angle	Light Beam	Efficiency	cd/lm	Connector
XM-L	Asymmetric deg	Streetligh...	92 %	-	-
XT-E	Asymmetric deg	Streetligh...	-	-	-
XM-L2	Asymmetric deg	Streetligh...	-	-	-
XP-G2	Asymmetric deg	Streetligh...	93 %	1.400	-
XP-L	sim: Asymmetric	Streetligh...	sim: 91 %	-	-
XP-L2	Asymmetric deg	Streetligh...	94 %	0.900	-

Luminaire: Ledil Oy CA11892_Strada-SQ-T-DW-XM-L-EU-TAPE CA11892_Strada-SQ-T-DW-XM-L-EU-TAPE
Lamps: 1 x Cree XM-L White




Luminaire: LEDiL Oy CA11892_STRADA-SQ-T-DW_(XP-G2) Eff: 93%
Lamps: 1 x CREE_XP-G2_(XPGBWT-H1-7B4-R4-0-04)_106.35lm@250mA_P=0.755748W_I=249.9mA




Luminaire: Ledil CA11892_STRADA-SQ-T-DW_(XP-L2)

Lamps: 1 x Cree_XP-L2_(XPLWT-00-0000-000HU630G)_115.75lm@250mA_P=0.721375W_I=0.25A



Luminaire: Ledil Oy CA11892_Strada-SQ-T-DW-XM-L-EU-TAPE CA11892_Strada-SQ-T-DW-XM-L-EU-TAPE
Lamps: 1 x Cree XM-L White




cd/klm

— C0 - C180 — C90 - C270

Luminaire: LEDiL Oy CA11892_STRADA-SQ-T-DW_(XP-G2) Eff. 93%

Lamps: 1 x CREE_XP-G2_(XPGBWT-H1-7B4-R4-0-04)_106.35lm@250mA_P=0.755748W_I=249.9mA




cd/klm

— C0 - C180

— C90 - C270

Luminaire: Ledil CA11892_STRADA-SQ-T-DW_(XP-L2)

Lamps: 1 x Cree_XP-L2_(XPLWT-00-0000-000HU630G)_115.75lm@250mA_P=0.721375W_I=0.25A



NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Ledil:

[CA11892_STRADA-SQ-T-DW](#)