

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

| LOC | | DIST | | REVISIONS | | | |
|-----|-----|--------------------------|--|-----------|-----|------|--|
| P | LTR | DESCRIPTION | | DATE | DWN | APVD | |
| | H | UPDATE PER ECO-11-013056 | | 23 JUN 11 | CAS | MKS | |

1 CONNECTOR BODY AND COUPLING NUT MATERIAL: 6061-T6 ALUMINUM, ELECTROLESS NICKEL PLATED PER SAE-AMS-C-26074 OR SAE-AMS-2404E
 LOCKING RING MATERIAL: BERYLLIUM COPPER, ELECTROLESS NICKEL PLATED PER SAE-AMS-C-26074 OR SAE-AMS-2404E
 INSULATOR MATERIAL: LIQUID CRYSTAL POLYMER (LCP) PER ASTM D5138 OR POLYPHENYLENE SULFIDE (PPS) PER ASTM D4067
 O-RING MATERIAL: FLUOROSILICONE

2 WIRE TERMINATION: 28 AWG SOLID, 30 AWG STRANDED WIRE OR SMALLER
 3 LUBRICATE O-RING WITH PARKER SUPER-O-LUBE PRIOR TO INSTALLATION
 4 THIS DRAWING ALSO IDENTIFIED AS NANONICS 303-0034

| | | | | | | | | |
|--|--|------------------|-----------|-----------|--|--|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN | M. STORRY | 20 MAY 99 | | TE Connectivity | | |
| DIMENSIONS: INCHES | | CHK | E. PAULUS | 11 JUN 99 | | NAME | | |
| | | APVD | S. KAIN | 27 JAN 00 | | PLUG ASSEMBLY, CIRCULAR, THREADED COUPLING, METAL, 44 POSITION | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | PRODUCT SPEC | | SIZE | | | | |
| 0 PLC ± - | | APPLICATION SPEC | | CAGE CODE | | DRAWING NO | | |
| 1 PLC ± - | | WEIGHT | | A2 | | OPJN9 | | |
| 2 PLC ± .010 | | CUSTOMER DRAWING | | SCALE | | 6:1 | | |
| 3 PLC ± .005 | | SCALE | | SHEET | | 1 OF 1 | | |
| 4 PLC ± - | | SCALE | | REV | | H | | |
| ANGLES ± 1° | | SCALE | | REV | | H | | |
| FINISH | | SCALE | | REV | | H | | |
| SEE NOTES | | SCALE | | REV | | H | | |
| SEE NOTES | | SCALE | | REV | | H | | |

1471-9 (3/11)

1589065

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TCM044PC0DM060](#)